


AC2950



Passive power distributor

ProcessLine 4SB IP69K



Depending on the version some LEDs are inactive



Application		
Design	AS-i oder IO-Link Spannungsverteiler	
Application	hygienic and wet areas in the food industry	
Electrical data		
Protection class	III	
Overcurrent detection	yes; (4400 mA ± 200 mA)	
AS-i operation		
Operating voltage	[V]	18...31.6 DC; (AS-i)
Current consumption	[mA]	4000; (AS-i)
Additional voltage supply	[V]	15...30 DC; (AUX)
Max. current consumption from additional supply	[mA]	4000; (AUX)
IO-Link operation		
Operating voltage	[V]	20...30 DC; (US)
Current consumption	[mA]	4000; (US)
Additional voltage supply	[V]	20...30 DC; (UA)



Passive power distributor

ProcessLine 4SB IP69K

Max. current consumption from additional supply	[mA]	4000; (UA)
---	------	------------

Operating conditions

Ambient temperature	[°C]	-25...60
Storage temperature	[°C]	-25...85
Max. relative air humidity	[%]	90; (non condensing)
Max. height above sea level	[m]	4000
Protection	IP 65; IP 66; IP 67; IP 69K; (operation with stainless steel protective caps: IP 69K)	
Protection rating (NEMA 250)	6P	
Pollution degree	2	
Chemical media	ISO 16750-5	HLP, CC, DB, DC, DD, CA
	NEMA 250 5.13.1	AA

Tests / approvals

EMC	EN 62026-2	
	IEC 61000-6-2	
Shock resistance	DIN EN 60068-2-27	
Vibration resistance	DIN EN 60068-2-64	
	DIN EN 60068-2-6	
MTTF	[ANN]	379

Mechanical data

Weight	[g]	284.8
Dimensions	[mm]	152 x 59.3 x 38.4
Materials	housing: PA grey; plugs and sockets: stainless steel (1.4404 / 316L)	

Displays / operating elements

Display	operation	LED, green AS-i / AUX / US / UA
	fault	LED, red

Electrical connection

Module connection	M12
-------------------	-----

Remarks

Pack quantity	1 pcs.
---------------	--------

Electrical connection - Power IN

Connector: M12; coding: A; Tightening torque: 0.6...0.8 Nm



AS-i operation

1	AS-i +
2	AUX -
3	AS-i -
4	AUX +

AC2950



Passive power distributor

ProcessLine 4SB IP69K

IO-Link operation

1	+ 24 V DC (US)
2	GND (UA)
3	GND (US)
4	+ 24 V DC (UA)

Electrical connection - Power OUT

Connector: M12; coding: A; Tightening torque: 0.6...0.8 Nm



AS-i operation 1...4

1	AS-i +
2	AUX -
3	AS-i -
4	AUX +
5	n.c.

IO-Link operation 1...4

1	+ 24 V DC (US)
2	GND (UA)
3	GND (US)
4	+ 24 V DC (UA)
5	n.c.