


RU6114



Incremental encoder with solid shaft

RU-3600-I24/K

Article no longer available - archive entry



Electrical data		
Operating voltage	[V]	10...30 DC
Current consumption	[mA]	150
Outputs		
Electrical design		HTL
Max. current load per output	[mA]	50
Switching frequency	[kHz]	160
Type of short-circuit protection		< 60 s
Phase difference A and B	[°]	90
Measuring/setting range		
Resolution		3600 resolution
Operating conditions		
Ambient temperature	[°C]	-20...85
Storage temperature	[°C]	-30...100
Max. relative air humidity	[%]	98
Protection		IP 64
Tests / approvals		
Shock resistance		100 g (6 ms)
Vibration resistance		15 g (55...2000 Hz)

RU6114




Incremental encoder with solid shaft

RU-3600-I24/K

Mechanical data		
Dimensions	[mm]	Ø 58 / L = 62
Materials		aluminium
Max. revolution, mechanical	[U/min]	12000
Max. starting torque	[Nm]	1
Reference temperature torque	[°C]	20
Shaft design		solid shaft
Shaft diameter	[mm]	6
Shaft material		steel (1.4104)
Max. shaft load axial (at the shaft end)	[N]	10
Max. shaft load radial (at the shaft end)	[N]	20
Fixing flange		synchro-flange

Electrical connection		
1	B inverted	
2	L+ sensor	
3	0 index	
4	0 index inverted	
5	A	
6	A inverted	
screen	housing	
7	failure inverted	
8	B	
9	n.c.	
10	0V (Un)	
11	0V sensor	
12	L+	

Connector: 1 x M23 (ifm 1001.4), radial



RU6114




Incremental encoder with solid shaft

RU-3600-I24/K

Diagrams and graphs

Pulse diagram



Output A

Output B

0 index

Article no longer available - archive entry