

AS-Interface control cabinet module

SmartLine25 4DI 4DO T C AUX



- 1 panel for labelling
- 2 addressing socket
- 3 DIN rail adapter



Application

Design	only for operation with AS-i masters with the profile M4
Application	Встановлення до шафи керування

Electrical data

Operating voltage	[V]	26.5...31.6 DC
Max. current consumption from AS-i	[mA]	50
Additional voltage supply	[V]	20 DC
Max. current consumption from additional supply	[mA]	4300; (AUX)
Integrated watchdog		yes

Inputs / outputs

Number of inputs and outputs	Number of digital inputs: 4; Number of digital outputs: 4
------------------------------	---

Inputs

Number of digital inputs		4
Input circuit of digital inputs		PNP; (type 2 according to IEC 61131-2)
Sensor supply of the inputs		AUX
Подача напруги	[V]	20...30; (DC)
Max. total current rating of inputs	[mA]	200



AS-Interface control cabinet module

SmartLine25 4DI 4DO T C AUX

Input current High	[mA]	6...10
Input current Low	[mA]	0...2
Switching level high	[V]	> 11
Digital inputs protected against short circuits		yes

Outputs

Number of digital outputs		4
Circuit		PNP
Voltage range DC	[V]	20...30; (AUX)
Max. current load per output	[mA]	1000; (utilisation category DC-12: 700 mA; utilisation category DC-13 (control of electromagnets): 20 W (IEC 60947-5-1))
Max. current load outputs total	[A]	4
Short-circuit proof		yes
Electrically separated		yes
Actuator supply outputs		AUX

Operating conditions

Ambient temperature	[°C]	-25...70
Max. relative air humidity	[%]	90; (non condensing)
Max. height above sea level	[m]	2000
Protection		IP 20
Pollution degree		2

Tests / approvals

EMC		EN 61000-6-2	
		EN 62026-2	
		EN 50581	
MTTF	[ANN]	186	
Notes		The device shall be supplied from an isolating source.; This voltage source must have a secondary UL-listed fuse (see enclosed sheet).; Alternatively, a class 2 power supply can be used to supply AUX.	

AS-i classification

AS-i version	3.0				
AS-i addressing	addressing socket				
Розширений режим адресації	yes				
AS-i master profile	M4				
AS-i profile	S-7.A.7				
AS-i I/O configuration	[hex]	7			
AS-i ID code	[hex]	A.7			
AS-i certificate pending	yes				
Assignment of the data bits	data bit	D0	D1	D2	D3
	input	I-1	I-2	I-3	I-4
	Output	O-1	O-2	O-3	O-4

Mechanical data

Weight	[g]	144.8
Type of mounting		mounting on DIN rail



AS-Interface control cabinet module

SmartLine25 4DI 4DO T C AUX

Dimensions	[mm]	108 x 25 x 105	
Materials		PC-GF20	
Displays / operating elements			
Display	switching status	LED, yellow I1...I4, O1...O4	
	operation	LED, green AS-i, AUX	
	errors	LED, red	
Аксессуары			
Accessories (optional)		connectors	
Remarks			
Pack quantity		1 pcs.	
Electrical connection			
pin header:			
Connection			

I-	I-	I-	I-
I1	I2	I3	I4
I+	I+	I+	I+

O-	O-	O-	O-
O1	O2	O3	O4
A+	A-	E+	E-

A+	AS-i +
A-	AS-i -
I+	Sensor supply +24V
I-	Sensor supply 0V
E+	external voltage supply for sensors/actuators +24V (AUX)
E-	external voltage supply for sensors/actuators 0V (AUX)
I1...I4	switching input sensor 1...4
O-	switching output actuator 0V
O1...O4	switching output actuator 1...4