


AC326A



AS-Interface dual sensor for pneumatic valve actuators

DUAL SENSOR T5 2SI 1DO T/3G



Product characteristics

Sensing range	[mm]	4
Dimensions	[mm]	55 x 60 x 35

Electrical data

Operating voltage	[V]	26.5...31.6 DC
Current consumption	[mA]	< 160
Protection class		III

Detection zone

Sensing range	[mm]	4
---------------	------	---

AC326A



AS-Interface dual sensor for pneumatic valve actuators

DUAL SENSOR T5 2SI 1DO T/3G

Operating distance target puck	[mm]	74
--------------------------------	------	----

Operating conditions

Ambient temperature	[°C]	-10...50
Protection		IP 67

Tests / approvals

ATEX marking	II 3G Ex nA IIC T6 Gc X	
Note on ATEX marking	only in conjunction with the impact protection housing	
EMC	EN 50295	
MTTF	[ANN]	310

AS-i classification

AS-i version		2.1
Розширений режим адресації		yes
AS-i I/O configuration	[hex]	7
AS-i ID code	[hex]	A.E

Mechanical data

Weight	[g]	766.5
Dimensions	[mm]	55 x 60 x 35
Materials	housing: PBT orange; cover: PC black; Impact protection housing: stainless steel	

Displays / operating elements

Display	operation	1 x LED, green
	function	1 x LED, yellow

Аксессуары

Items supplied	Impact protection housing	
	Mounting plate: 1	
	socket head screws: 2 x M5 x 35	

Remarks

Pack quantity	1 pcs.
---------------	--------

Electrical connection - plug

Connector: 1 x M12; coding: A; Moulded body: stainless steel



Elektrischer Anschluss

1	AS-i+
3	AS-i-

AC326A



AS-Interface dual sensor for pneumatic valve actuators

DUAL SENSOR T5 2SI 1DO T/3G

Electrical connection - socket

Connector: 1 x M12; coding: A; Moulded body: stainless steel



Connection

Ausgänge

3	external voltage -
4	switching output +
1, 2, 5	nicht belegt