


AC570A



AS-Interface Airbox with quick mounting technology

AirBox 5/3 closed 4DI-Y II 3D



Application		
Application		AS-i ATEX module
Electrical data		
Operating voltage	[V]	26.5...31.6 DC
Max. current consumption from AS-i	[mA]	280
Integrated watchdog		yes
Inputs / outputs		
Number of inputs and outputs		Number of digital inputs: 4; Number of pneumatic outputs: 2
Inputs		
Number of digital inputs		4
Input circuit of digital inputs		PNP
Sensor supply of the inputs		AS-i
Подача напруги	[V]	20...30; (via flat cable)

AC570A



AS-Interface Airbox with quick mounting technology

AirBox 5/3 closed 4DI-Y II 3D

Max. total current rating of inputs	[mA]	200
Input current High	[mA]	6...10
Input current Low	[mA]	0...2
Switching level high	[V]	> 11
Digital inputs protected against short circuits		yes

Outputs

Electrical design	AS-i
Number of pneumatic outputs	2

Operating conditions

Ambient temperature	[°C]	-10...50
Protection		IP 50

Tests / approvals

ATEX marking	Ⓔ II 3D Ex tc IIIB T80°C Dc X IP50		
EMC	EN 50295		
	IEC 61000-6-2		
MTTF	[ANN]	258	

AS-i classification

AS-i version	2.11; 3.0				
AS-i addressing	addressing socket				
Розширений режим адресації	yes				
AS-i master profile	M2; M3; M4				
AS-i profile	S-7.A.E				
AS-i I/O configuration	[hex]	7			
AS-i ID code	[hex]	A.E			
AS-i certificate pending	yes				
Assignment of the data bits	data bit	D0	D1	D2	D3
	input	1	2	3	4
	socket	I-1/2	I-1/2 I-2	I-3/4	I-3/4 I-4
	pin	4	2 4	4	2 4
	pneumatic output	2	4	-	-

Mechanical data

Weight	[g]	421
Type of mounting		quick mounting
Materials		PA; POM; piercing contacts: CuSn6 nickel-plated and tin-plated
Pneumatic system		1 x 5/3-way slide valve (free from overlapping); middle position blocked
Operating pressure range	[bar]	3...8
Operating pressure range	[MPa]	0.3...0.8
Air flow at 6/5 bar	[l/min]	400
Permissible compressed air		non-lubricated compressed air class 6-3-1; lubricated compressed air class 6-3-4
Manual override		pressing/releasing or pressing/turning/locking
Tube fittings		8 mm
Exhaust		exhaust can be discharged through tube connection

AC570A



AS-Interface Airbox with quick mounting technology

AirBox 5/3 closed 4DI-Y II 3D

Displays / operating elements		
Display	operation	LED, green
	errors	LED, red
	function	LED, yellow
Electrical connection		
Module connection	Приладдя	
Аксессуары		
Items supplied	lower part	
Accessories (optional)	Mounting plate:, E74999	
	Module lower part:, E75000	
	Protective cap: M12, E73004	
	Ущільнювальна заглушка:, E75231	
	Impact protection housing:, E7000A	
	silencer:, E75232	
	Push-in L-fitting:, E75228	
	Push-in T-fitting:, E75227	
Remarks		
Remarks	Mechanical protection has to be implemented.	
	Otherwise the unit must be installed together with the impact protection housing (E7000A).	
	If not pneumatically operated, E75231 sealing plug must be inserted.	
	Avoid ingress of dirt and dust.	
	Do not connect any of the following points to an external potential:	
	L-, L+, I-1, I-2, I-3, I-4	
	The connections are electrically connected with the AS-i cable.	
	Please see the notes on compressed air and EMC/ESD under "Downloads"	
Pack quantity	1 pcs.	

AC570A




AS-Interface Airbox with quick mounting technology

AirBox 5/3 closed 4DI-Y II 3D


Electrical connection

quick mounting technology for AS-i flat cable: ; three orientations possible

Connection



Connector: M12; coding: A





AS-Interface Airbox with quick mounting technology


AirBox 5/3 closed 4DI-Y II 3D

Connection

Inputs	
socket I-1/2	
1	Sensor supply L+
2	data input 2
3	Sensor supply L-
4	data input 1
5	not used
socket I-2	
1	Sensor supply L+
2	not used
3	Sensor supply L-
4	data input 2
5	not used
socket I-3/4	
1	подача напруги L+
2	data input 4
3	Sensor supply L-
4	data input 3
5	not used
socket I-4	
1	Sensor supply L+
2	not used
3	Sensor supply L-
4	data input 4
5	not used

Diagrams and graphs

Pneumatic symbol



1 x 5/3-way slide valve (free from overlapping); middle position blocked