
VSM104

Acceleration sensor

VIBRATION SENSOR



Product characteristics		
Measuring range of vibration	[g]	-40...40
Frequency range	[Hz]	0...4500
Measuring principle		capacitive
Application		
Special feature		Drag chain suitability
Electrical data		
Bias voltage DC	[V]	11...16
Operating current	[mA]	4...6
Min. insulation resistance	[MΩ]	100; (500 V DC)
Protection class		III
Reverse polarity protection		yes
Sensor type		microelectromechanical system (MEMS)
Measuring/setting range		
Measuring range of vibration	[g]	-40...40
Frequency range	[Hz]	0...4500
Measuring principle		capacitive
Max. transverse sensitivity	[%]	5
Number of measurement axes		3
Accuracy / deviations		
Accuracy		0...3 kHz: +/- 10 % 3...4.5 kHz: 3 dB
Measuring sensitivity		100 mV/g
Linearity deviation		2

VSM104

Acceleration sensor

VIBRATION SENSOR

[% of the span]			
Operating conditions			
Ambient temperature	[°C]	-30...85	
Storage temperature	[°C]	-30...100	
Protection		IP 67; IP 68; IP 69K	
Tests / approvals			
EMC		DIN EN 61000-6-2	
		DIN EN 61000-6-3	
Shock resistance		DIN EN 60068-2-27	50 g 11 ms
Vibration resistance		DIN EN 60068-2-6	20 g / 10...3000 Hz
MTTF	[years]	529	
UL approval		Enclosure type	Type 1
		power supply	Limited Voltage/Current
		UL Approval no.	L003
		File number UL	E251902
Mechanical data			
Weight	[g]	427.6	
Type of mounting		mounting screw	
Dimensions	[mm]	26.2 x 47.3 x 11.6	
Materials		housing: stainless steel (1.4404 / 444)	
Tightening torque	[Nm]	3.5	
Drag chain suitability		yes	
Drag chain suitability		bending radius for flexible use	min. 10 x cable diameter
		bending radius for fixed installation	min. 4 x cable diameter
Accessories			
Items supplied		socket head screw: 1 x M5 x 12	
Remarks			
Pack quantity		1 pcs.	

Electrical connection

Cable: 10 m, PUR, Ø 4.9 mm; Maximum cable length: 250 m; screen (connected to the housing); 5 x 0.14 mm²

brown IEPE X
white IEPE Z
blue GND
black self-test
grey IEPE Y
yellow screen