




AS-Interface ClassicLine module with quick mounting technology

ClassicLine 2DI 2DO-Y IP67



Application		
Application		field installation
Electrical data		
Operating voltage	[V]	26.5...31.6 DC; ("supply class 2" to cULus)
Max. current consumption from AS-i	[mA]	150
Max. current load total	[A]	4
Integrated watchdog		yes
Inputs / outputs		
Number of inputs and outputs		Number of digital inputs: 2; Number of digital outputs: 2
Inputs		
Number of digital inputs		2
Input circuit of digital inputs		PNP
Sensor supply of the inputs		AS-i
Подача напруги	[V]	18...30; (via flat cable)
Max. total current rating of inputs	[mA]	100
Input current High	[mA]	6...10
Input current Low	[mA]	0...2
Switching level high	[V]	> 11
Digital inputs protected against short circuits		yes



AS-Interface ClassicLine module with quick mounting technology

ClassicLine 2DI 2DO-Y IP67

Outputs					
Number of digital outputs	2				
Circuit	PNP				
Voltage range DC [V]	15...30; (to PELV; via flat cable)				
Max. current load per output [mA]	2000; (utilisation category DC-13 (control of electromagnets): 40 W (IEC 60947-5-1))				
Short-circuit proof	yes				
Electrically separated	yes				
Actuator supply outputs	AUX				
Operating conditions					
Ambient temperature [°C]	-25...70				
Protection	IP 67				
Tests / approvals					
EMC	EN 50295				
	IEC 61000-6-2				
MTTF [ANN]	188				
AS-i classification					
AS-i version	2.11; 3.0				
AS-i addressing	addressing socket				
Розширений режим адресації	no				
AS-i master profile	M2; M3; M4				
AS-i profile	S-3.0.E				
AS-i I/O configuration [hex]	3				
AS-i ID code [hex]	0.E				
Assignment of the data bits	data bit	D0	D1	D2	D3
	input	1	2	-	-
	socket	I-1	I-2	-	-
	pin	2+4	2+4	-	-
	Output	-	-	3	4
	socket	-	-	O-3/4	O-3/4 O-4
	pin	-	-	4	2 4
Mechanical data					
Weight [g]	195.5				
Type of mounting	AS-i flat cables directly connectable				
Materials	PA; piercing contacts: CuSn6 nickel-plated and tin-plated				
Displays / operating elements					
Display	operation		LED, green		
	errors		LED, red		
	function		LED, yellow		
Electrical connection					
Module connection	Приладдя				
Аксессуары					
Items supplied	lower part				
Accessories (optional)	Protective cap: M12, E73004				




AS-Interface ClassicLine module with quick mounting technology


ClassicLine 2DI 2DO-Y IP67

Remarks	
Remarks	Inputs and outputs must be electrically isolated.
	Do not connect any of the following points to an external potential:
	I-, I+, I1, I2
	The connections are electrically connected with the AS-i cable.
Pack quantity	1 pcs.

Electrical connection
quick mounting technology for AS-i flat cable: ; three orientations possible

Electrical connection - Inputs	
Connector: M12; coding: A	
	
1	Inputs
2+4	Sensor supply L+
3	data input internally bridged
5	Sensor supply L-
5	not used

Electrical connection - Outputs
Connection





AS-Interface ClassicLine module with quick mounting technology

ClassicLine 2DI 2DO-Y IP67

Connector: M12

Outputs	
1	not used
	socket O-3/4
2	switching output 4
3	external voltage AUX -
4	switching output 3
5	not used
	socket O-3
1	not used
2	not used
3	external voltage AUX -
4	switching output 4
5	not used