


E11315



Vtič adapterja

ESTGH050MSS00,5E05 (M20)



Električni podatki		
Obratovalna napetost	[V]	< 125 AC/DC
Pogoji okolja		
Temperatura okolice	[°C]	-25...85
Zaščita		IP 68
Mehanski podatki		
Teža	[g]	27,3
Mere	[mm]	18 x 18 x 19
Namestitveni navoj		M20
Materiali		medenina ponikljano
Material ulitega dela		medenina, ponikljano
Opombe		
Embalažna enota		1 Kosov



Vtič adapterja


ESTGH050MSS00,5E05 (M20)

Električni priključek

Kabel: 0,5 m, PVC; 4 x 0,25 mm² + 1 x 0,5 mm²

Električni priključek - vtič

Spojnik: 1 x M12, ravno; kodiranje: A; Oblikovano telo: medenina, ponikljano; Pritezni vrtilni moment: ...0,6 Nm; navoj M20 Pritezni vrtilni moment: ...2 Nm



Priključek

1	BN
2	WH
3	BU
4	BK
5	GN/YE

	Barva žil :
BK =	črn
BN =	rjavo
BU =	modro
GN =	zeleno
WH =	belo
YE =	rumeno