

AC1391




AS-Interface EtherCAT gateway with PLC

ControllerE M4 1Mstr ECAT

Article no longer available - archive entry

Alternative articles: AC1433

When selecting an alternative article and accessories please note that technical data may differ!



Application	
Application	decentralised controller; EtherCat gateway
Electrical data	
Operating voltage [V]	24 DC
Current consumption [mA]	< 400
Max. current consumption from AS-i [mA]	10
Max. power consumption [VA]	10
Number of AS-i masters	1
Interfaces	
Communication interface	RS232; Ethernet



AS-Interface EtherCAT gateway with PLC

ControllerE M4 1Mstr ECAT

Ethernet - EtherCAT		
Protocol		EtherCAT
Usage type		data transmission
RS232		
Number of R232 interfaces		1
Transmission rate		9600...115200 Baud
Connector type		RJ11
Usage type		programming
Note on interfaces		electrically isolated
Operating conditions		
Ambient temperature	[°C]	0...60
Storage temperature	[°C]	-20...70
Protection		IP 20
AS-i classification		
AS-i version		2.11; 3.0
AS-i master profile		M4
Mechanical data		
Weight	[g]	552.4
Housing		housing for DIN rail mounting
Dimensions	[mm]	131 x 107 x 86
Materials		aluminium; steel sheet galvanised
Displays / operating elements		
Display	function	3 x LED, red
		4 x LED, green
		2 x LED, yellow
		full graphic LCD display
Remarks		
Pack quantity		1 pcs.
Electrical connection		
Connection		

