


AL1950



IO-Link master with IoT interface

IO-Link Master CL IoT 8P IP20



Application		
Application		I/O modules for use in the control cabinet
Electrical data		
Operating voltage	[V]	20...30 DC; (US ; to SELV/PELV)
Current consumption	[mA]	300...3900; (US)
Protection class		III
Sensor supply US		
Max. current load total	[A]	3.6
Inputs / outputs		
Total number of inputs and outputs		16; (configurable)
Number of inputs and outputs		Number of digital inputs: 8; Number of digital outputs: 8
Inputs		
Number of digital inputs		8; (IO-Link Port Class A)
Switching level high	[V]	11...30
Switching level low	[V]	0...5
Digital inputs protected against short circuits		yes
Outputs		
Number of digital outputs		8; (IO-Link Port Class A)
Max. current load per output	[mA]	300



IO-Link master with IoT interface

IO-Link Master CL IoT 8P IP20

Short-circuit proof	yes
Interfaces	
Communication interface	Ethernet; IO-Link
Ethernet - Internet of Things	
Transmission standard	10Base-T; 100Base-TX
Transmission rate	10 MBit/s; 100 MBit/s
Protocol	MQTT JSON
Factory settings	IP address: 169.254.x.x
	subnet mask: 255.255.0.0
	gateway IP address: 0.0.0.0
	MAC address: see type label
Note on interfaces	Secure protocol: HTTPS
IO-Link Master	
Transmission type	COM1 (4,8 kBaud); COM2 (38,4 kBaud); COM3 (230,4 kBaud)
IO-Link revision	1.1
Number of ports class A	8
Operating conditions	
Ambient temperature [°C]	-25...65
Storage temperature [°C]	-25...85
Max. relative air humidity [%]	90
Protection	IP 20
Tests / approvals	
EMC	EN 61000-6-2
	EN 61000-6-4
MTTF [ANN]	91
Mechanical data	
Weight [g]	327.5
Materials	housing: PA orange
Аксессуары	
Items supplied	cage clamps: 9
Remarks	
Remarks	For further information please see the operating instructions.
Pack quantity	1 pcs.
Electrical connection	
подача напруги X31	
1	GND (US)
2	GND (US)
3	+ 24 V DC (US)
4	+ 24 V DC (US)
IO-Link Port Class A X01...X08	
1	Sensor supply (US) L+
2	digital input
3	Sensor supply (US) L-
4	C/Q IO-Link



IO-Link master with IoT interface

IO-Link Master CL IoT 8P IP20

Electrical connection - Ethernet

Connector: RJ45

