


AL3000



PROFINET-Switch

ETH Switch SL PN-A 6P IP67



Depending on the version some LEDs are inactive



Application	
Design	unmanaged switch for field applications
Application	für PROFINET-Netzwerke
Electrical data	
Operating voltage [V]	8...32 DC; (US; to SELV/PELV)
Nominal voltage DC [V]	12 / 24
Current consumption [mA]	100; (US; 24 V: 50 mA)
Protection class	III
Reverse polarity protection	yes
Interfaces	
Communication interface	Ethernet
Number of Ethernet interfaces	6

AL3000



PROFINET-Switch

ETH Switch SL PN-A 6P IP67

Operating conditions		
Ambient temperature	[°C]	-25...70
Storage temperature	[°C]	-25...85
Max. relative air humidity	[%]	90
Max. height above sea level	[m]	4000
Protection		IP 65; IP 66; IP 67
Protection rating (NEMA 250)		6P
Degree of soiling		2
Chemical media	ISO 16750-5	AA, BA, BD, HLP, CC, DB, DC, DD, CA
	NEMA 250 5.13.1	AA

Tests / approvals			
EMC	UN/ECE-R10 noise emission and noise interference:	100 V/m	
	DIN EN 61000-6-2 ESD		
	DIN EN 61000-6-4 Burst		
	ISO 7637-2 pulse 1	severity level 4 / function state C (12 V)	
	ISO 7637-2 pulse 2a	severity level 4 / function state A (12 V)	
	ISO 7637-2 pulse 2b	severity level 4 / function state C (12 V)	
	ISO 7637-2 pulse 3a	severity level 4 / function state A (12 V)	
	ISO 7637-2 pulse 3b	severity level 4 / function state A (12 V)	
	ISO 7637-2 pulse 4	severity level 4 / function state A (12 V)	
	ISO 7637-2 pulse 5a	severity level 3 / function state A (12 V)	
	ISO 7637-2 pulse 1	severity level 4 / function state C (24 V)	
	ISO 7637-2 pulse 2a	severity level 4 / function state A (24 V)	
	ISO 7637-2 pulse 2b	severity level 4 / function state C (24 V)	
	ISO 7637-2 pulse 3a	severity level 4 / function state A (24 V)	
	ISO 7637-2 pulse 3b	severity level 4 / function state A (24 V)	
	ISO 7637-2 pulse 4	severity level 4 / function state A (24 V)	
	Shock resistance	DIN EN 60068-2-27	
	Fast temperature change	EN 60068-2-30	
		EN 60068-2-78	
EN 60068-2-52			
Vibration resistance	DIN EN 60068-2-64		
	DIN EN 60068-2-6		
	EN 60068-2-27		

Mechanical data		
Weight	[g]	296.1
Materials		housing: PA; socket: brass nickel-plated
Sealing material		FKM

Remarks		
Remarks		For further information please see the operating instructions.
Pack quantity		1 pcs.

Electrical connection - Ethernet		
Connector: 6 x M12; Sealing: FKM		

AL3000



PROFINET-Switch

ETH Switch SL PN-A 6P IP67



X01...X06

1	TX +
2	RX +
3	TX -
4	RX -
5	not used

Electrical connection - voltage supply

Connector: 1 x M12



X31

1	+ 24 V DC (US)
2	not used
3	GND (US)
4	not used