




IO-Link CompactLine module

IO-Link module 8 x 2 DI IP 67



Electrical data

Operating voltage	[V]	18...30 DC; ("supply class 2" to cULus)
Current consumption	[mA]	< 50
Sensor supply US		
Current rating per port	[A]	0.1

Inputs / outputs

Number of inputs and outputs	Number of digital inputs: 16
------------------------------	------------------------------

Inputs

Number of digital inputs	16; (8 x 2)
Input circuit of digital inputs	PNP



IO-Link CompactLine module

IO-Link module 8 x 2 DI IP 67

Sensor supply of the inputs	IO-Link
Input current limitation [mA]	15
Input current High [mA]	6...10
Input current Low [mA]	0...2
Switching level high [V]	> 11
Digital inputs protected against short circuits	yes

Interfaces

Communication interface	IO-Link				
Supported DeviceIDs	<table> <tr> <th>Type of operation</th><th>DeviceID</th></tr> <tr> <td>default</td><td>555</td></tr> </table>	Type of operation	DeviceID	default	555
Type of operation	DeviceID				
default	555				

IO-Link Device

Transmission type	COM2 (38,4 kBaud)
IO-Link revision	1.1
SDCI standard	IEC 61131-9
SIO mode	no
Process data analogue	1
Process data binary	24
Min. process cycle time [ms]	2.9

Operating conditions

Ambient temperature [°C]	-25...70				
Protection	IP 67				
Protection rating (NEMA 250)	6P				
Chemical media	<table> <tr> <td>ISO 16750-5</td><td>AA, BA, BD, HLP, CC, DB, DC, DD, CA</td></tr> <tr> <td>NEMA 250 5.13.1</td><td>AA</td></tr> </table>	ISO 16750-5	AA, BA, BD, HLP, CC, DB, DC, DD, CA	NEMA 250 5.13.1	AA
ISO 16750-5	AA, BA, BD, HLP, CC, DB, DC, DD, CA				
NEMA 250 5.13.1	AA				

Tests / approvals

EMC	<table> <tr> <td>EN 61000-6-2</td><td></td></tr> <tr> <td>EN 61000-6-3</td><td></td></tr> <tr> <td>IEC 61131-9</td><td></td></tr> </table>	EN 61000-6-2		EN 61000-6-3		IEC 61131-9	
EN 61000-6-2							
EN 61000-6-3							
IEC 61131-9							
MTTF [ANN]	164						

Mechanical data

Weight [g]	382.5
Materials	PA; socket: brass nickel-plated; O-ring: FKM
Sealing material	FKM

Displays / operating elements

Display	<table> <tr> <td>operation</td><td>LED, green</td></tr> <tr> <td>errors</td><td>LED, red</td></tr> <tr> <td>function</td><td>LED, yellow</td></tr> </table>	operation	LED, green	errors	LED, red	function	LED, yellow
operation	LED, green						
errors	LED, red						
function	LED, yellow						

Аксессуары

Accessories (optional)	Stainless steel sleeve, for installation in case of high mechanical stress , E70402
------------------------	---

Remarks

Remarks	For use in NFPA 79 applications only The device is to be operated to IO-Link specification V1.1.2. The maximum cable length of the IO-Link cable is 20 m.
Pack quantity	1 pcs.



IO-Link CompactLine module

IO-Link module 8 x 2 DI IP 67

Electrical connection - IO-Link


Connector: M12; coding: A



1	UB +
2	not used
3	UB -
4	IO-Link

Electrical connection - Process connection

Connector: M12; coding: A; Sealing: FKM



	Inputs X1.0...X1.7
1	Sensor supply +24 V
2	IN 2
3	Sensor supply 0 V
4	IN 1
5	not used