




Pressure sensor with display

PN-010-RER34-LFPKG/US/ IV

phase-out article
Discontinuation date: 03/31/2024



- 1 alphanumeric display 4-digit
- 2 LEDs Display unit / switching status
- 3 programming button



Product characteristics				
Number of inputs and outputs	Number of digital outputs: 1; Number of analogue outputs: 1			
Measuring range	-1...10 bar	-14.5...145 psi	-100...1000 kPa	-0.1...1 MPa
Process connection	threaded connection G 3/4 external thread			
Application				
Special feature	Gold-plated contacts			
Application	for industrial applications			
Media	liquids and gases			
Medium temperature [°C]	-15...80			
Min. bursting pressure	150 bar	2175 psi	15 MPa	
Pressure rating	75 bar	1087 psi	7.5 MPa	
Vacuum resistance [mbar]	-1000			
Type of pressure	relative pressure			
No dead space	yes			
Electrical data				
Operating voltage [V]	18...36 DC; (to SELV/PELV)			
Current consumption [mA]	< 50			
Min. insulation resistance [MΩ]	100; (500 V DC)			
Protection class	III			



Pressure sensor with display

PN-010-RER34-LFPKG/US/ IV

Reverse polarity protection	yes
Overvoltage protection	yes; (< 40 V)
Power-on delay time [s]	0.3
Integrated watchdog	yes

Inputs / outputs

Number of inputs and outputs	Number of digital outputs: 1; Number of analogue outputs: 1
------------------------------	---

Outputs

Total number of outputs	2
Output signal	switching signal; analogue signal; (configurable)
Electrical design	PNP
Number of digital outputs	1
Output function	normally open / normally closed; (parameterisable)
Max. voltage drop switching output DC [V]	2
Permanent current rating of switching output DC [mA]	250
Switching frequency DC [Hz]	< 170
Number of analogue outputs	1
Analogue current output [mA]	4...20
Max. load [Ω]	(U _b - 10 V) / 20 mA
Analogue voltage output [V]	0...10
Min. load resistance [Ω]	2000
Short-circuit protection	yes
Type of short-circuit protection	pulsed

Measuring/setting range

Measuring range	-1...10 bar	-14.5...145 psi	-100...1000 kPa	-0.1...1 MPa
Set point SP	-0.9...10 bar	-12...145 psi		-0.09...1 MPa
Reset point rP	-0.95...9.95 bar	-13...144 psi		-0.095...0.995 MPa
In steps of	0.05 bar	1 psi		0.005 MPa

Accuracy / deviations

Switch point accuracy [% of the final value]	< ± 0,5
Repeatability [% of the final value]	< ± 0,1; (with temperature fluctuations < 10 K)
Characteristics deviation [% of the final value]	< ± 0,5
Hysteresis deviation [% of the final value]	< ± 0,25
Long-term stability [% of the final value]	< ± 0,05

Response times

Delay time programmable dS, dr [s]	0; 0,2...50
Max. response time analogue output [ms]	3



Pressure sensor with display

PN-010-RER34-LFPKG/US/ IV

Software / programming		
Parameter setting options	hysteresis / window; normally open / normally closed; switch-on/ switch-off delay; Damping; Display unit; current/voltage output	
Operating conditions		
Ambient temperature	[°C]	-15...80
Storage temperature	[°C]	-40...100
Protection	IP 67	
Tests / approvals		
EMC	EN 61000-4-2 ESD	4 kV CD / 8 kV AD
	EN 61000-4-3 HF radiated	10 V/m
	EN 61000-4-4 Burst	2 kV
	EN 61000-4-5 Surge	0,5/1 kV
	EN 61000-4-6 HF conducted	10 V
Shock resistance	DIN IEC 68-2-27	50 g (11 ms)
Vibration resistance	DIN IEC 68-2-6	20 g (10...2000 Hz)
MTTF	[years]	229.64
Pressure Equipment Directive	Sound engineering practice; can be used for group 2 fluids; group 1 fluids on request	
Mechanical data		
Weight	[g]	283.5
Materials	stainless steel (304/1.4301); stainless steel (316L/1.4404); PC; PBT; PEI; FKM; PTFE	
Materials (wetted parts)	stainless steel (316L/1.4404); ceramics (99.9 % Al2O3); FKM	
Min. pressure cycles	100 million	
Process connection	threaded connection G 3/4 external thread	
Displays / operating elements		
Display	Display unit	3 x LED, green
	switching status	LED, yellow
	function display	alphanumeric display, 4-digit
	measured values	alphanumeric display, 4-digit
Remarks		
Pack quantity	1 pcs.	
Electrical connection		
Connector: 1 x M12; coding: A; Contacts: gold-plated		
		

PY9964



Pressure sensor with display

PN-010-RER34-LFPKG/US/ IV

Connection



OUT1 switching output
OUT2 analogue output
 colours to DIN EN 60947-5-2
 Core colours :
BK = black
BN = brown
BU = blue
WH = white