



## Incremental encoder with solid shaft

RV-3600-I24/N2

Article no longer available - archive entry



- 1 reference mark  
2 M3 Depth 5 mm



### Product characteristics

Resolution	3600 resolution
Shaft design	solid shaft
Shaft diameter [mm]	10

### Electrical data

Operating voltage [V]	10...30 DC
Current consumption [mA]	150

### Outputs

Electrical design	HTL
Max. current load per output [mA]	50
Switching frequency [kHz]	300
Type of short-circuit protection	< 60 s
Phase difference A and B [°]	90

### Measuring/setting range

Resolution	3600 resolution
------------	-----------------

### Operating conditions


Ambient temperature [°C]	-30...85
Note on ambient temperature	for firmly laid cable
Storage temperature [°C]	-30...100
Protection	IP 64

# RV6115



## Incremental encoder with solid shaft

RV-3600-I24/N2

Tests / approvals		
Shock resistance		100 g (6 ms)
Vibration resistance		10 g (55...2000 Hz)
Mechanical data		
Dimensions	[mm]	Ø 58 / L = 46
Materials		aluminium
Max. revolution, mechanical [U/min]		12000
Max. starting torque	[Nm]	1
Reference temperature torque	[°C]	20
Shaft design		solid shaft
Shaft diameter	[mm]	10
Shaft material		steel (1.4104)
Max. shaft load axial (at the shaft end)	[N]	10
Max. shaft load radial (at the shaft end)	[N]	20
Electrical connection		
Cable: 2 m, PUR; radial		
brown		A
green		A inverted
grey		B
pink		B inverted
red		0 index
black		0 index inverted
blue		L+ sensor
white		0V sensor
brown/green		L+ (Up)
white/green		0V (Un)
lilac		failure inverted
screen		housing
Diagrams and graphs		
Pulse diagram		 <p>Output A Output B 0 index</p>
Article no longer available - archive entry		