




Compact evaluation unit for speed monitoring

DIA3010-ZPKG/30-3000 I/MIN/6M

Article no longer available - archive entry



Product characteristics

Electrical design	PNP
Output function	normally open
Sensing range [mm]	10
Dimensions [mm]	M30 x 1.5 / L = 81

Application

Application	simple evaluation of rotating and linear movement with regard to underspeed; blocking
-------------	---

Electrical data

Nominal voltage DC [V]	10...36
Current consumption [mA]	< 15
Reverse polarity protection	yes

Outputs

Total number of outputs	1
Electrical design	PNP
Output function	normally open
Max. voltage drop switching output DC [V]	2.5
Permanent current rating of switching output DC [mA]	250
Short-time current rating of switching output [mA]	250
Short-circuit proof	yes
Overload protection	yes

Detection zone

Sensing range [mm]	10
Sensing range adjustable	no

Measuring/setting range


Setting range [Imp/min]	30...3000
-------------------------	-----------



Compact evaluation unit for speed monitoring

DIA3010-ZPKG/30-3000 I/MIN/6M

Accuracy / deviations		
Correction factor	steel: 1 / stainless steel: 0.7 / brass: 0.5 / aluminium: 0.4 / copper: 0.3	
Hysteresis	[X01]	10
Response times		
Start-up delay	[s]	15
Max. damping frequency	[Imp/min]	15000
Software / programming		
Adjustment of the switch point	multiturn potentiometer	
Operating conditions		
Ambient temperature	[°C]	-25...80
Protection	IP 67	
Mechanical data		
Mounting	flush mountable	
Dimensions	[mm]	M30 x 1.5 / L = 81
Thread designation	M30 x 1.5	
Materials	brass special coating; PBT	
Tightening torque	[Nm]	50
Displays / operating elements		
Display	switching status	1 x LED, green
Electrical connection		
Cable: 6 m, PVC; 3 x 0.5 mm²		
Connection		



Core colours :

BK = black

BN = brown

BU = blue