

DI522A



Compact evaluation unit for speed monitoring

DIA3010-ZPKG/US/3D/5S



1 potentiometer



Product characteristics

Electrical design	PNP
Output function	normally open
Sensing range [mm]	10
Dimensions [mm]	M30 x 1.5 / L = 92.3

Application

Application	simple evaluation of rotating and linear movement with regard to underspeed; blocking
-------------	---

Electrical data

Nominal voltage DC [V]	10...36
Current consumption [mA]	< 20
Protection class	III
Reverse polarity protection	yes

Outputs

Total number of outputs	1
Electrical design	PNP
Output function	normally open
Max. voltage drop switching output DC [V]	2.5
Permanent current rating of switching output DC [mA]	250
Short-time current rating of switching output [mA]	250
Short-circuit proof	yes
Overload protection	yes

Detection zone

Sensing range [mm]	10
Sensing range adjustable	no
Operating distance [mm]	0...8.1

Measuring/setting range

Setting range [Imp/min]	5...3600
-------------------------	----------

DI522A



Compact evaluation unit for speed monitoring

DIA3010-ZPKG/US/3D/5S

Measuring principle	inductive		
Accuracy / deviations			
Correction factor	steel: 1 / stainless steel: 0.7 / brass: 0.5 / aluminium: 0.4 / copper: 0.3		
Hysteresis	[X01]	10	
Response times			
Start-up delay	[s]	5	
Max. damping frequency	[Imp/min]	18000	
Software / programming			
Adjustment of the switch point	multiturn potentiometer		
Operating conditions			
Ambient temperature	[°C]	-25...60	
Storage temperature	[°C]	-25...60	
Protection	IP 65; IP 67		
Tests / approvals			
Approval	IECEX BVS 17.0094X		
ATEX marking	 II 3D Ex tc IIIC T80°C Dc X		
EMC	EN 60947-5-2		
Shock resistance	DIN EN 60947-5-2		
Vibration resistance	DIN EN 60947-5-2		
MTTF	[ANN]	3262	
Mechanical data			
Weight	[g]	267	
Mounting	flush mountable		
Dimensions	[mm]	M30 x 1.5 / L = 92.3	
Thread designation	M30 x 1.5		
Materials	brass special coating; PA; stainless steel; TPE-U		
Displays / operating elements			
Display	switching status		1 x LED, green
	input signal		1 x LED, yellow
Аксессуары			
Items supplied	lock nuts: 2		
Electrical connection			
Connector: 1 x M12; coding: A			
			

DI522A



Compact evaluation unit for speed monitoring

DIA3010-ZPKG/US/3D/5S

Connection

