


DTE601



Compact RFID device with fieldbus interface

DTRHF HLRWPNUS03



Application

Radio approval for	USA; Canada; EU/RED; Australia; China; South Korea; Japan; Taiwan; Singapore; Malaysia; India; В'єтнам
Note on radio approval	The list of countries applying the European Radio Equipment Directive 2014/53/EU (RED) can be found under "Downloads".

Electrical data

Operating voltage [V]	19.2...28.8 DC
Current consumption [mA]	500
Protection class	III
Operating frequency [MHz]	13,56
RFID standard	ISO 15693

Outputs

Max. current load per output [mA]	100; (max.)
-----------------------------------	-------------

Detection zone

Distance write/read head front [mm]	600		
Distance write/read head side [mm]	850		
Note on distance write/read head	100%		transmission power
Distance to the ID tag [mm]	50 mm tag	:	≤ 150
	ISO card	:	≤ 180

Interfaces

Communication interface	Ethernet
Ethernet - PROFINET	
Protocol	PROFINET
Usage type	data transmission

DTE601



Compact RFID device with fieldbus interface

DTRHF HLRWPNUS03

Ethernet - TCP/IP	
Protocol	TCP/IP
Factory settings	IP address: 192.168.0.79
	subnet mask: 255.255.255.0
	gateway IP address: 192.168.0.100
Usage type	parameter setting

Operating conditions	
Ambient temperature	[°C] -20...60
Storage temperature	[°C] -25...80
Protection	IP 67

Tests / approvals		
Shock resistance	IEC 60028-2-27	40 g (6 ms) / bump
		50 g (11 ms) / single shock
Vibration resistance	EN 60068-2-6	2 g (10...150 Hz)
MTTF	[ANN]	130

Mechanical data	
Weight	[g] 641.5
Dimensions	[mm] 113 x 118.5 x 50
Materials	PBT / PC; stainless steel; aluminium

Displays / operating elements		
Display	подача напруги	1 x LED, green
	LED bar display	4 x LED, yellow signal strength ID tag
	status	2 x LED, green/red fieldbus interface
	status	2 x LED, green/yellow Ethernet

Remarks	
Pack quantity	1 pcs.

Electrical connection - Ethernet

Connector: 2 x M12; coding: D



ETH1 / ETH2	
1	TD+
2	RD+
3	TD-
4	RD-

DTE601




Compact RFID device with fieldbus interface

DTRHF HLRWPNUS03

Electrical connection - подача напруги

Connector: 1 x M12; coding: A



PWR

1	L+
2	digital input/output 2
3	L-
4	digital input/output 1
5	not used