


DTE605



Compact RFID device with fieldbus interface

DTRHF HLRWITUS03



Application			
Radio approval for	USA; Canada; South Korea; Japan; Taiwan; Singapore; China; EU/RED; India; Malaysia; В'єтнам		
Note on radio approval	The list of countries applying the European Radio Equipment Directive 2014/53/EU (RED) can be found under “Downloads”.		
Electrical data			
Operating voltage	[V]	19.2...28.8 DC	
Current consumption	[mA]	500	
Protection class		III	
Operating frequency	[MHz]	13,56	
RFID standard		ISO 15693	
Outputs			
Max. current load per output	[mA]	100; (max.)	
Detection zone			
Distance write/read head front	[mm]	600	
Distance write/read head side	[mm]	850	
Note on distance write/read head		100%	transmission power
Distance to the ID tag	[mm]	50 mm tag	≤ 150
		ISO card	≤ 180
Interfaces			
Communication interface	Ethernet		
Ethernet - Internet of Things			
Transmission standard	10Base-T; 100Base-TX		
Transmission rate	10 MBit/s; 100 MBit/s		
Protocol	MQTT JSON		

DTE605



Compact RFID device with fieldbus interface

DTRHF HLRWITUS03

Factory settings	IP address: 192.168.0.79
	subnet mask: 255.255.255.0
	gateway IP address: 192.168.0.100
Usage type	parameter setting; data transmission

Operating conditions	
Ambient temperature	[°C] -20...60
Storage temperature	[°C] -25...80
Protection	IP 67

Tests / approvals		
Shock resistance	IEC 60028-2-27	40 g (6 ms) / bump
		50 g (11 ms) / single shock
Vibration resistance	EN 60068-2-6	2 g (10...150 Hz)
UL approval	Ta	-20...60 °C
	Enclosure type	Type 1
	подача напруги	Limited Voltage/Current
	File number UL	E205959

Mechanical data	
Weight	[g] 645.1
Dimensions	[mm] 113 x 118.5 x 50
Materials	PBT / PC; stainless steel; aluminium

Displays / operating elements		
Display	подача напруги	1 x LED, green
	LED bar display	4 x LED, yellow signal strength ID tag
	status	2 x LED, green/red fieldbus interface
	status	2 x LED, green/yellow Ethernet

Remarks	
Pack quantity	1 pcs.

Electrical connection - Ethernet

Connector: 2 x M12; coding: D



ETH1 / ETH2	
1	TD+
2	RD+
3	TD-
4	RD-

DTE605




Compact RFID device with fieldbus interface

DTRHF HLRWITUS03

Electrical connection - подача напруги

Connector: 1 x M12; coding: A



PWR	
1	L+
2	digital input/output 2
3	L-
4	digital input/output 1
5	not used