


DTE905



Compact RFID device

DTRUHFA HLRWITUS04



Application

Radio approval for	USA; Canada; Mexico
--------------------	---------------------

Electrical data

Operating voltage	[V]	19.2...28.8 DC
Current consumption	[mA]	500
Power consumption	[W]	8.6
Protection class		III
Operating frequency	[MHz]	902...928
RFID standard		EPC Class1 GEN2/ISO 18000-63
Transmission power EIRP	[mW]	200; (maximum: 250 mW)

Outputs

Max. current load per output	[mA]	100; (max.)
------------------------------	------	-------------

Interfaces

Communication interface	Ethernet
-------------------------	----------

Ethernet - Internet of Things

Transmission standard	10Base-T; 100Base-TX
Transmission rate	10 MBit/s; 100 MBit/s
Protocol	MQTT JSON
Factory settings	IP address: 192.168.0.79 subnet mask: 255.255.255.0 gateway IP address: 192.168.0.100
Usage type	parameter setting; data transmission

Operating conditions

Ambient temperature	[°C]	-20...55
Note on ambient temperature		with mounting plate and cooling element: -20...60 °C
Storage temperature	[°C]	-25...80

DTE905



Compact RFID device

DTRUHFA HLRWITUS04

Protection	IP 67
------------	-------

Tests / approvals

Shock resistance	IEC 60028-2-27	40 g (6 ms) / bump
		50 g (11 ms) / single shock
Vibration resistance	EN 60068-2-6	2 g (10...150 Hz)
UL approval	Ta	-20...60 °C
	Enclosure type	Type 1
	подача напруги	Limited Voltage/Current
	File number UL	E205959

Mechanical data

Weight	[g]	692.7
Dimensions	[mm]	113 x 118.6 x 50
Materials	housing: aluminium; PBT / PC; stainless steel	

Displays / operating elements

Display	подача напруги	1 x LED, green
	LED bar display	4 x LED, yellow signal strength ID tag
	status	2 x LED, green/red fieldbus interface
	status	2 x LED, green/yellow Ethernet

Remarks

Pack quantity	1 pcs.
---------------	--------

Electrical connection - Ethernet

Connector: 2 x M12; coding: D




ETH1 / ETH2

1	TD+
2	RD+
3	TD-
4	RD-

Electrical connection - подача напруги

Connector: 1 x M12; coding: A



DTE905



Compact RFID device

DTRUHFA HLRWITUS04

PWR	
1	L+
2	digital input/output 2
3	L-
4	digital input/output 1
5	not used