


Article no longer available - archive entry

Alternative articles: AC2027

When selecting an alternative article and accessories please note that technical data may differ!



- 1 tube connection Ø 8 mm
2 panel for labelling

**Electrical data**

Operating voltage [V]	26.5...31.6 DC
Current consumption [mA]	< 150
Integrated watchdog	yes

Inputs / outputs

Number of inputs and outputs	Number of digital inputs: 2; Number of pneumatic outputs: 2
------------------------------	---

Inputs

Number of digital inputs	2
Input circuit of digital inputs	PNP
Sensor supply of the inputs	AS-i
Подача напруги [V]	20...30
Max. total current rating of inputs [mA]	100
Input current High [mA]	> 3
Input current Low [mA]	< 1.5
Switching level high [V]	> 10
Digital inputs protected against short circuits	yes



AS-Interface AirBox

AirBox/2DI/2PO M12

Outputs						
Electrical design		AS-i				
Number of pneumatic outputs		2				
Operating conditions						
Ambient temperature		[°C] 0...55				
Note on ambient temperature		with special compressed air treatment: < 0 °C				
Protection		IP 67				
Tests / approvals						
EMC		EN 50295				
AS-i classification						
AS-i profile		S-3.F				
AS-i I/O configuration		[hex] 3				
AS-i ID code		[hex] F				
AS-i certificate		10501				
Assignment of the data bits		data bit	D0	D1	D2	D3
		Inputs / outputs	I-1	I-2	O-3	O-4
Mechanical data						
Type of mounting		screw mounting				
Materials		PBT				
Pneumatic system		2 x 3/2-way seat valves				
Operating pressure range		[bar] 2...8				
Operating pressure range		[MPa] 0.2...0.8				
Note on working pressure range		incl. possible pressure peaks				
Air flow at 6/5 bar		[l/min] 350				
Air flow at 6/0 bar		[l/min] 550				
Permissible compressed air		filtered (5 µm); lubricated (ISO-VG10) or not lubricated				
Tube fittings		Legris LF 3000/8				
Exhaust		exhaust can be discharged through tube connection				
Displays / operating elements						
Display		operation			LED, green	
		function			LED, yellow	
Remarks						
Remarks		Please see the notes on compressed air and EMC/ESD under "Downloads"				
Pack quantity		1 pcs.				




AS-Interface AirBox

AirBox/2DI/2PO M12

Electrical connection

contact pins to module lower part, FK / PG:

Connector: M12; coding: A



	Inputs
1	Sensor supply L+
2+4	data input internally bridged
3	Sensor supply L-