




AS-Interface module

EMS-Module 4DI M12

Article no longer available - archive entry

Alternative articles: AC5205
When selecting an alternative article and accessories please note that technical data may differ!



1 panel for labelling




Electrical data		
Operating voltage	[V]	26.5...31.6 DC
Current consumption	[mA]	< 235
Inputs / outputs		
Number of inputs and outputs	Number of digital inputs: 4	
Inputs		
Number of digital inputs	4	
Input circuit of digital inputs	NPN	
Sensor supply of the inputs	AS-i	
Подача напруги	[V]	20...30
Max. total current rating of inputs	[mA]	200
Input current High	[mA]	> 5
Input current Low	[mA]	< 1.5
Switching level high	[V]	> 10
Digital inputs protected against short circuits	yes	
Outputs		
Electrical design	AS-i	



AS-Interface module

EMS-Module 4DI M12

Operating conditions						
Ambient temperature		[°C]	-25...85			
Protection			IP 67			
Tests / approvals						
EMC		EN 50295				
AS-i classification						
AS-i profile		S-0.0				
AS-i I/O configuration		[hex]	0			
AS-i ID code		[hex]	0			
Assignment of the data bits		data bit	D0	D1	D2	D3
		socket	I-1	I-2	I-3	I-4
		pin	2+4	2+4	2+4	2+4
Mechanical data						
Type of mounting		AS-i interface to FC and SC lower parts				
Materials		PBT				
Displays / operating elements						
Display		operation		LED, green		
		function		LED, yellow		
Remarks						
Remarks		The module can be re-addressed up to 15 times.				
Pack quantity		1 pcs.				
Electrical connection						
contact pins to module lower part, FK / PG:						
Connector: M12; coding: A						
						



AS-Interface module

EMS-Module 4DI M12

Connection

