




Multifunction display for monitoring revolution, speed and time

DISPLAY/FX460/ANALOG/AC/DC



panel cutout 91 x 43 mm



Product characteristics

Dimensions [mm] 48 x 112 x 116

Application

Application universal evaluation and display for all physical units which can be derived from pulse sequences

Electrical data

Frequency AC	[Hz]	50...60
Operating voltage	[V]	115...230 AC / 18...30 DC
Current consumption	[mA]	100

Inputs / outputs

Number of inputs and outputs Number of digital inputs: 2; Number of digital outputs: 4; Number of analogue outputs: 1

Inputs

Number of digital inputs	2
--------------------------	---

Outputs

Number of digital outputs	4	
Number of analogue outputs	1	
Analogue current output	[mA]	4...20
Max. load	[Ω]	270
Analogue voltage output	[V]	-10...10
Overload protection		yes

Operating conditions

Ambient temperature	[°C]	-20...60
Storage temperature	[°C]	-25...70
Protection		IP 65
Protection rating terminals		IP 20

Tests / approvals

EMC	EN 61000-6-2	
	EN 61000-6-3	
	EN 61000-6-4	




Multifunction display for monitoring revolution, speed and time

DISPLAY/FX460/ANALOG/AC/DC

Mechanical data		
Weight	[g]	352
Type of mounting		panel cutout: 91 x 43 mm
Dimensions	[mm]	48 x 112 x 116
Materials		Noryl UL94-V-0

Displays / operating elements		
Display	colour display	full graphic LCD display, touch screen

Electrical connection		
screw terminals:		
Connection		



NC: not used