


AC542A



AS-Interface Airbox with quick mounting technology

AirBox 2x3/2 4DI-Y II 3D



Application		
Application		AS-i ATEX module
Electrical data		
Operating voltage	[V]	26.5...31.6 DC
Max. current consumption from AS-i	[mA]	280
Integrated watchdog		yes
Inputs / outputs		
Number of inputs and outputs		Number of digital inputs: 4; Number of pneumatic outputs: 2
Inputs		
Number of digital inputs		4
Input circuit of digital inputs		PNP
Sensor supply of the inputs		AS-i
Подача напруги	[V]	20...30; (via flat cable)



AS-Interface Airbox with quick mounting technology

AirBox 2x3/2 4DI-Y II 3D

Max. total current rating of inputs	[mA]	200			
Input current High	[mA]	6...10			
Input current Low	[mA]	0...2			
Switching level high	[V]	> 11			
Digital inputs protected against short circuits		yes			
Outputs					
Electrical design		AS-i			
Number of pneumatic outputs		2			
Operating conditions					
Ambient temperature	[°C]	-10...50			
Protection		IP 50			
Tests / approvals					
ATEX marking		 II 3D Ex tc IIIB T80°C Dc X IP50			
EMC		EN 50295			
MTTF	[ANN]	288			
AS-i classification					
AS-i version		2.11; 3.0			
AS-i addressing		addressing socket			
Розширений режим адресації		no			
AS-i master profile		M2; M3; M4			
AS-i profile		S-7.F.F			
AS-i I/O configuration	[hex]	7			
AS-i ID code	[hex]	F.F			
AS-i certificate pending		yes			
Assignment of the data bits	data bit	D0	D1	D2	D3
	input	1	2	3	4
	socket	I-1/2	I-1/2 / I-2	I-3/4	I-3/4 / I-4
	pin	4	2 4	4	2 4
	pneumatic output	-	-	2	4
Mechanical data					
Weight	[g]	417.5			
Type of mounting		quick mounting			
Materials		PA; POM; piercing contacts: CuSn6 nickel-plated and tin-plated			
Pneumatic system		2 x 3/2-way slide valves (free from overlapping)			
Operating pressure range	[bar]	2...8			
Operating pressure range	[MPa]	0.2...0.8			
Air flow at 6/5 bar	[l/min]	500			
Permissible compressed air		non-lubricated compressed air class 6-3-1; lubricated compressed air class 6-3-4			
Manual override		pressing/releasing or pressing/turning/locking			
Tube fittings		8 mm			
Exhaust		exhaust can be discharged through tube connection			

AC542A



AS-Interface Airbox with quick mounting technology

AirBox 2x3/2 4DI-Y II 3D

Displays / operating elements		
Display	operation	LED, green
	errors	LED, red
	function	LED, yellow
Electrical connection		
Module connection	Приладдя	
Аксессуары		
Items supplied	lower part	
Accessories (optional)	Mounting plate:, E74999	
	Module lower part:, E75000	
	Protective cap: M12, E73004	
	Ущільнювальна заглушка:, E75231	
	Impact protection housing:, E7000A	
	silencer:, E75232	
	Push-in L-fitting:, E75228	
	Push-in T-fitting:, E75227	
Remarks		
Remarks	Mechanical protection has to be implemented.	
	Otherwise the unit must be installed together with the impact protection housing (E7000A).	
	If not pneumatically operated, E75231 sealing plug must be inserted.	
	Avoid ingress of dirt and dust.	
	Do not connect any of the following points to an external potential:	
	L-, L+, I-1, I-2, I-3, I-4	
	The connections are electrically connected with the AS-i cable.	
	Please see the notes on compressed air and EMC/ESD under "Downloads"	
Pack quantity	1 pcs.	

AC542A




AS-Interface Airbox with quick mounting technology

AirBox 2x3/2 4DI-Y II 3D


Electrical connection

quick mounting technology for AS-i flat cable: ; three orientations possible

Connection



Connector: M12; coding: A



AS-Interface Airbox with quick mounting technology


AirBox 2x3/2 4DI-Y II 3D

Connection

Inputs	
socket I-1/2	
1	Sensor supply L+
2	data input 2
3	Sensor supply L-
4	data input 1
5	not used
socket I-2	
1	Sensor supply L+
2	not used
3	Sensor supply L-
4	data input 2
5	not used
socket I-3/4	
1	подача напруги L+
2	data input 4
3	Sensor supply L-
4	data input 3
5	not used
socket I-4	
1	Sensor supply L+
2	not used
3	Sensor supply L-
4	data input 4
5	not used

Diagrams and graphs

Pneumatic symbol



2 x 3/2-way slide valves (free from overlapping)