


DX2051



Multifunction display for monitoring analogue standard signals

DISPLAY/AX460/DC



panel
cutout 91 x 43 mm



Product characteristics

Dimensions [mm] 48 x 112 x 116

Application

Application displaying and monitoring analogue signals; e.g. pressure sensors, temperature sensors or flow sensors

Electrical data

Operating voltage [V] 18...30 DC
Current consumption [mA] 100

Inputs / outputs

Number of inputs and outputs Number of analogue inputs: 2

Inputs

Number of analogue inputs 2; (Spannungs- oder Stromeingang)
Analogue input (current) [mA] 0...20
Analogue input (voltage) [V] -10...10
Resolution of analogue input 16 bit
Precision analogue input [%] 0,1

Operating conditions

Ambient temperature [°C] -20...60
Storage temperature [°C] -25...70
Protection IP 65
Protection rating terminals IP 20

Tests / approvals

EMC EN 61000-6-2
EN 61000-6-3
EN 61000-6-4

Mechanical data

Weight [g] 300.5
Type of mounting panel cutout: 91 x 43 mm

DX2051



Multifunction display for monitoring analogue standard signals

DISPLAY/AX460/DC

Dimensions	[mm]	48 x 112 x 116
Materials		Noryl UL94-V-0


Displays / operating elements

Display	colour display	full graphic LCD display, touch screen
---------	----------------	--

Electrical connection

screw terminals:

Connection



NC not used