


E3M154



Connection cable

CONNECTION CABLE M12 21M



Application		
Special feature	Screened cable; Drag chain suitability	
Design	for 3D Smart sensor mobile with analogue video output PAL	
Electrical data		
Operating voltage	[V]	< 25 AC / < 60 DC
Protection class	III	
Operating conditions		
Ambient temperature	[°C]	-40...80
Protection	IP 67; IP 69K	
Mechanical data		
Weight	[g]	1076.5
Materials	housing: PUR; Sealing: FKM; contact pins: CuSn6 nickel-plated and tin-plated	
Material nut	stainless steel (1.4305 / 303)	
Drag chain suitability	yes	
Drag chain suitability	bending radius for fixed installation	≥ 60 mm
Remarks		
Pack quantity	1 pcs.	



Connection cable

CONNECTION CABLE M12 21M

Electrical connection - plug

Connector: 1 x M12, angled; coding: A; Locking: stainless steel (1.4305 / 303)



Electrical connection

Cable: 21 m, black, Ø 6 mm, shielded; 3 x 0.25 mm²

Connection



- 1: screen
- 2: not used
- 3: coax screen
- 4: coax cable core
- 5: not used

Electrical connection - plug

Connector: 1 x M12, straight; coding: A; Locking: stainless steel (1.4305 / 303)

