




Connection cable

VDOGQ090PLS0003E03STGF040MSS



Electrical data		
Operating voltage	[V]	< 60 AC / < 75 DC
Protection class		III
Operating conditions		
Ambient temperature	[°C]	-25...85
Protection		IP 50
Mechanical data		
Weight	[g]	113.9
Materials		PUR
Moulded-body material		PUR
Material nut		brass, nickel-plated
Remarks		
Pack quantity		1 pcs.
Electrical connection		
Cable: 3 m, PVC, black, Ø 5 mm; 3 x 0.25 mm² (32 x Ø 0.1 mm)		
Electrical connection - plug		
Connector: 1 x M8, straight; coding: A; Moulded body: PUR; Locking: brass, nickel-plated		




E11572



Connection cable

VDOGQ090PLS0003E03STGF040MSS

Connection



Electrical connection - socket

Connector: 1 x Sub D, straight; Moulded body: PUR; Locking: brass, nickel-plated

