


AL2241



IO-Link input module

IO-Link Module 10x2 DI M12 IP69K



Electrical data

Operating voltage	[V]	18...30 DC
Current consumption	[mA]	100...1100; (US)
Protection class		III

Sensor supply US

Current rating per port	[A]	0.1
-------------------------	-----	-----

Inputs / outputs

Number of inputs and outputs	Number of digital inputs: 20
------------------------------	------------------------------

Inputs

Number of digital inputs	20; (10 x 2 PNP type 2 according to IEC 61131-2)
--------------------------	--

AL2241



IO-Link input module

IO-Link Module 10x2 DI M12 IP69K

Sensor supply of the inputs	IO-Link
Подача напруги [V]	16...30

Interfaces		
Communication interface	IO-Link	
SDCI standard	IEC 61131-9	
Transmission type	COM2 (38,4 kBaud)	
IO-Link revision	1.1	
SIO mode	no	
Required master port type	A	
Min. process cycle time [ms]	4.3	
Supported DeviceIDs	Type of operation	DeviceID
	default	940

Operating conditions		
Ambient temperature [°C]	-25...60	
Storage temperature [°C]	-25...70	
Max. relative air humidity [%]	90	
Max. height above sea level [m]	2000	
Protection	IP 65; IP 67; IP 69K; (operation with stainless steel protective caps: IP 69K)	
Protection rating (NEMA 250)	6P	
Pollution degree	2	
Chemical media	ISO 16750-5	HLP, CC, DB, DC, DD, CA
	NEMA 250 5.13.1	AA

Tests / approvals		
EMC	EN 61000-6-2	
	EN 61000-6-3	
	IEC 61131-9	
Shock resistance	DIN EN 60068-2-27	
Vibration resistance	DIN EN 60068-2-64	
	DIN EN 60068-2-6	
MTTF [ANN]	140	

Mechanical data		
Weight [g]	406	
Materials	housing: PA grey; socket: stainless steel (1.4404 / 316L)	
Sealing material	EPDM	

Displays / operating elements		
Display	operation	1 x LED, green
	fault	1 x LED, red
	function	1 x LED, yellow

Аксессуары	
Accessories (optional)	protective cap for M12 sockets
Remarks	
Pack quantity	1 pcs.



IO-Link input module

IO-Link Module 10x2 DI M12 IP69K

Electrical connection - IO-Link

Connector: 1 x M12; coding: A




X1

1	+ 24 V DC (US)
2	not used
3	GND (US)
4	IO-Link

Electrical connection - Inputs

Connector: 10 x M12; coding: A; Sealing: EPDM



X1.0...X1.9

1	Sensor supply + 24 V DC (US)
2	digital input DI2
3	Sensor supply GND (US)
4	digital input DI1
5	not used