


Fibre optic through-beam sensor

FE-30-P-A-M6/2M

Article no longer available - archive entry

Alternative articles: E20328

When selecting an alternative article and accessories please note that technical data may differ!



Application

Function principle	Through-beam sensor
--------------------	---------------------

Detection zone

Range with fibre-optic amplifier type	OIF
---------------------------------------	-----

OIF

Range of fibre optics [mm]	270
----------------------------	-----

Operating conditions

Ambient temperature [°C]	-20...80
--------------------------	----------

Mechanical data

Version of sensing head	straight
Sensing head thread	M6
Sensing head length [mm]	35
Total length [mm]	2000
Min. bending radius [mm]	30
Fibre arrangement	●

E20217



Fibre optic through-beam sensor

FE-30-P-A-M6/2M

Materials	Adapter: PA
Fibre material	glass
Fibre head material	aluminium
Fibre sheath material	PVC
Remarks	
Pack quantity	1 pcs.