


IO-Link CompactLine module

IO-Link Module 6x2 DO M12 IP67



Application

Application	I/O modules for field applications
-------------	------------------------------------

Electrical data

Operating voltage	[V]	18...30 DC; (US)
Current consumption	[mA]	50; (US)
Protection class		III
Additional voltage supply	[V]	18...30 DC; (UA)
Max. current consumption from additional supply	[mA]	3600; (UA)

Inputs / outputs

Number of inputs and outputs	Number of digital outputs: 12
------------------------------	-------------------------------

Outputs

Number of digital outputs	12; (6 x 2)
Output function	PNP
Max. current load per output [mA]	1800
Max. current load outputs total [A]	3.6; (Max. current load per output side: 1800 mA)
Electrically separated	yes

AL2330



IO-Link CompactLine module

IO-Link Module 6x2 DO M12 IP67

Interfaces		
Communication interface	IO-Link	
Supported DeviceIDs	Type of operation	DeviceID
	default	893
IO-Link Device		
Transmission type	COM2 (38,4 kBaud)	
IO-Link revision	1.1	
SDCI standard	IEC 61131-9	
SIO mode	no	
Min. process cycle time	[ms]	5.6
Operating conditions		
Ambient temperature	[°C]	-25...60
Storage temperature	[°C]	-25...70
Max. relative air humidity	[%]	90
Max. height above sea level	[m]	2000
Protection	IP 65; IP 67	
Protection rating (NEMA 250)	6P	
Pollution degree	2	
Chemical media	ISO 16750-5	AA, BA, BD, HLP, CC, DB, DC, DD, CA
	NEMA 250 5.13.1	AA
Tests / approvals		
EMC	EN 61000-6-2	
	EN 61000-6-3	
	IEC 61131-9	
Shock resistance	DIN EN 60068-2-27	
Vibration resistance	DIN EN 60068-2-64	
	DIN EN 60068-2-6	
MTTF	[ANN]	63
Mechanical data		
Weight	[g]	303
Dimensions	[mm]	26 x 59.3 x 152
Materials	housing: PA; socket: brass nickel-plated	
Sealing material	FKM	
Displays / operating elements		
Display	operation	LED, green
	errors	LED, red
	function	LED, yellow
Аксессуары		
Accessories (optional)	захисні заглушки M12	
Remarks		
Pack quantity	1 pcs.	



IO-Link CompactLine module

IO-Link Module 6x2 DO M12 IP67

Electrical connection - IO-Link

Connector: M12; coding: A



X1

1	+ 24 V DC (US)
2	not used
3	GND (US)
4	IO-Link

Electrical connection - Outputs

Connector: M12; coding: A; Sealing: FKM



X1.0...X1.5

1	not used
2	DO2
3	GND (UAE)
4	DO1
5	not used

Electrical connection - подача напруги

Connector: M12; coding: A



X31

1	+ 24 V DC (UAE)
2	GND (UAE)
3	GND (UAE)
4	+ 24 V DC (UAE)