


E30430



IO-Link display

IO-LINK INLINE DISPLAY 1,44"



Application

Special feature	Gold-plated contacts
Application	display of all process values of a connected sensor

Electrical data

Operating voltage	[V]	18...30 DC
Current consumption	[mA]	< 47
Min. insulation resistance	[MΩ]	100; (500 V DC)
Protection class		III
Reverse polarity protection		yes

Software / programming

Parameter setting options	display, indication
---------------------------	---------------------

Interfaces

Communication interface	IO-Link	
Transmission type	COM2 (38,4 kBaud)	
IO-Link revision	1.1	
SDCI standard	IEC 61131-9	
Profiles	Smart Sensor: Process Data Variable; Device Identification, Device Diagnosis	
SIO mode	no	
Required master port type	A	
Min. process cycle time	[ms]	11.2
Supported DeviceIDs	Type of operation	DeviceID
	default	694

Operating conditions

Ambient temperature	[°C]	0...60
---------------------	------	--------

E30430



IO-Link display

IO-LINK INLINE DISPLAY 1,44"

Storage temperature	[°C]	-20...80
Protection		IP 65; IP 67

Tests / approvals

EMC	DIN EN 61000-6-2	
	DIN EN 61000-6-4	
Shock resistance	DIN EN 60068-2-27	5 g (11 ms)
Vibration resistance	DIN EN 60068-2-6	5 g (10...50 Hz)
MTTF	[ANN]	397

Mechanical data

Weight	[g]	204
Materials		stainless steel (1.4404 / 316L); PC; PBT-GF30; PPS; FKM

Displays / operating elements

Display		colour display 1,44", 128 x 128 pixels
		2 x LED, yellow

Аксессуары

Items supplied		Y-подібні розподільники:, E12481
----------------	--	----------------------------------

Remarks

Pack quantity		1 pcs.
---------------	--	--------

Electrical connection

Connector: 1 x M12; Contacts: gold-plated		
---	--	--