




Welding adapter for process sensors

WELDING ADAPT D60/G1 LEAK PORT



- 1 G1 internal thread Aseptoflex Vario
 2 Leakage port
 3 sealing area



EHEDG Certified

Application

Design	with leakage port
Installation	for thin wall thicknesses
Pressure rating [bar]	25
Note on pressure rating	for the connection sensor - adapter

Tests / approvals

Pressure Equipment Directive	A possible classification to PED depends on the application and has to be carried out by the user / operator.
Safety instructions	The compatibility between medium and product material has to be checked in all applications.

Mechanical data

Weight [g]	156
Materials (wetted parts)	stainless steel (1.4435 / 316L) ; surface characteristics : Ra<0,4 / Rz 4
Sensor connection	G 1 internal thread Aseptoflex Vario
Process connection	welding adapter Ø 60 mm
Sealing	Gasket

Аксессуары

Items supplied	O-ring: 1 x 24 x 2, EPDM, FDA compliant, E30054
Accessories (optional)	O-ring: 1 x 24 x 2, FKM, FDA compliant, E30123

Remarks

Pack quantity	1 pcs.
---------------	--------