


# E43212



## Coaxial pipe for level sensors

LR COAX TUBE G3/4 L450



1 fixing bracket for centring piece

**CRN**

Application	
Design	for level sensors LR
Medium temperature [°C]	-40...200
Pressure rating [bar]	16
Vacuum resistance [mbar]	-1000
MAWP (for applications according to CRN) [bar]	16
Mechanical data	
Weight [g]	290.5
Materials	Coaxial pipe: stainless steel (1.4301 / 304); Sealing: NBR reinforced fibre; Centring piece: PPS reinforced fibre; fixing bracket: stainless steel (1.4310 / 301)
Sensor connection	threaded connection G 3/4 internal thread
Process connection	threaded connection G 3/4 external thread
Length L [mm]	450
Аксессуары	
Items supplied	Sealing: 1
Remarks	
Pack quantity	1 pcs.