


Evaluation unit for speed monitoring

D100/ 12VDC

Article no longer available - archive entry



1 mounting on DIN rail



Product characteristics

| | |
|-----------------|-------------------------------|
| Housing | housing for DIN rail mounting |
| Dimensions [mm] | 75 x 55 x 110 |

Application

| | |
|-------------|--|
| Application | universal evaluation of pulse sequences with regard to overspeed and underspeed; rotational speed monitoring |
|-------------|--|

Electrical data

| | |
|-------------------------------------|---------------------|
| Nominal voltage DC [V] | 24 |
| Nominal voltage tolerance [%] | 10 |
| Nominal voltage tolerance 2 [%] | 10 |
| Auxiliary energy for sensors DC [V] | 24; (≤ 30 mA) |

Inputs / outputs

| | |
|------------------------------|----------------------------|
| Number of inputs and outputs | Number of relay outputs: 1 |
|------------------------------|----------------------------|

Outputs

| | |
|-------------------------|--------------------------|
| Number of relay outputs | 1 |
| Contact rating | 8 A / 1250 VA / 250 V AC |

Measuring/setting range

| | |
|-------------------------|----------|
| Setting range [Imp/min] | 5...5000 |
|-------------------------|----------|

Accuracy / deviations

| | |
|---------------------|---------|
| Hysteresis [X01] | 5...100 |
| Repeatability [X01] | 1 |

Response times

| | |
|--------------------|----------|
| Start-up delay [s] | 0.5...15 |
|--------------------|----------|



Evaluation unit for speed monitoring

D100/ 12VDC


| Software / programming | | |
|--------------------------------|---|-------------------------------|
| Adjustment of the switch point | fine adjustment within the range with potentiometer | |
| Operating conditions | | |
| Ambient temperature | [°C] | -20...70 |
| Protection | | IP 40 |
| Protection rating terminals | | IP 20 |
| Mechanical data | | |
| Weight | [g] | 0.272 |
| Housing | | housing for DIN rail mounting |
| Dimensions | [mm] | 75 x 55 x 110 |
| Materials | | plastics |
| Displays / operating elements | | |
| Display | switching status | LED, green |
| | operation | 1 x LED, green |

Evaluation unit for speed monitoring

D100/ 12VDC

Electrical connection

Connection



| | |
|-----|----------------------------|
| 01: | not used |
| 02: | not used |
| 03: | DC Sensor supply (-) |
| 04: | sensor signal pnp |
| 05: | DC Sensor supply (+) |
| 06: | 24 V DC supply voltage (-) |
| 07: | 24 V DC supply voltage (+) |
| 08: | not used |
| 09: | not used |
| 10: | not used |
| 11: | not used |
| 12: | relay normally closed |
| 13: | relay common |
| 14: | relay normally open |
| 15: | 12 V DC supply voltage (+) |
| 16: | 12 V DC supply voltage (-) |