


E80379



RFID tag

ID-TAG/Label 80X50/03 - 896 bit



Electrical data

Operating frequency	[MHz]	13,56
Memory size	[bit]	896
Memory type		EEPROM
Chip type		ICODE SLIX
Number of blocks		28
Block size	[Byte]	4
Unique Identification Number (UID)	[Byte]	8
RFID standard		ISO 15693
Max. read cycles		unlimited
Max. write cycles		100000

Tests / approvals

Radio approval	ISO 15693
----------------	-----------

Mechanical data

Weight	[g]	939.8
Type of mounting		installation on non-metal materials; (self-adhesive)
Dimensions	[mm]	50 x 80 x 0.1
Materials		PP; adhesive: HL2

Remarks

Pack quantity	500 pcs.
---------------	----------

E80379



RFID tag

ID-TAG/Label 80X50/03 - 896 bit

Other data

Reading distance when mounted on non-metal (mm)

ANT410 / DTI410	22
ANT411 / DTI411	35
ANT420 / DTI420 / DTM424 / DTI424 / DTM426	20
ANT421 / DTI421 / DTM425 / DTI425 / DTM427	65
ANT430 / DTI430 / DTM434 / DTI434 / DTM436	50
ANT431 / DTI431 / DTM435 / DTI435 / DTM437	85
ANT513 / DTI513 / DTC510	120
ANT515 / DTI515 / ANT516 / DTI516	50
ANT600 / DTI600	250