

DI521A



Compact evaluation unit for speed monitoring

DIA3010-ZPKG/US/3D



1 potentiometer



Product characteristics		
Electrical design		PNP
Output function		normally open
Sensing range	[mm]	10
Dimensions	[mm]	M30 x 1.5 / L = 92.3
Application		
Application	simple evaluation of rotating and linear movement with regard to underspeed; blocking	
Electrical data		
Nominal voltage DC	[V]	10...36
Current consumption	[mA]	< 20
Protection class		III
Reverse polarity protection		yes
Outputs		
Total number of outputs		1
Electrical design		PNP
Output function		normally open
Max. voltage drop switching output DC	[V]	2.5
Permanent current rating of switching output DC	[mA]	250
Short-time current rating of switching output	[mA]	250
Short-circuit proof		yes
Overload protection		yes
Detection zone		
Sensing range	[mm]	10
Sensing range adjustable		no
Operating distance	[mm]	0...8.1
Measuring/setting range		
Setting range	[Imp/min]	5...3600



Compact evaluation unit for speed monitoring

DIA3010-ZPKG/US/3D

Measuring principle	inductive		
Accuracy / deviations			
Correction factor	steel: 1 / stainless steel: 0.7 / brass: 0.5 / aluminium: 0.4 / copper: 0.3		
Hysteresis	[X01]	10	
Response times			
Start-up delay	[s]	15	
Max. damping frequency	[Imp/min]	18000	
Software / programming			
Adjustment of the switch point	multiturn potentiometer		
Operating conditions			
Ambient temperature	[°C]	-25...60	
Storage temperature	[°C]	-25...60	
Protection		IP 65; IP 67	
Tests / approvals			
Approval	IECEX BVS 17.0094X		
ATEX marking	 II 3D Ex tc IIIC T80°C Dc X		
EMC	EN 60947-5-2		
Shock resistance	DIN EN 60947-5-2		
Vibration resistance	DIN EN 60947-5-2		
MTTF	[ANN]	3262	
Mechanical data			
Weight	[g]	264	
Mounting		flush mountable	
Dimensions	[mm]	M30 x 1.5 / L = 92.3	
Thread designation		M30 x 1.5	
Materials		brass special coating; PA; stainless steel; TPE-U	
Displays / operating elements			
Display	switching status	1 x LED, green	
	input signal	1 x LED, yellow	
Аксессуары			
Items supplied	lock nuts: 2		
Electrical connection			
Connector: 1 x M12; coding: A			
			

DI521A



Compact evaluation unit for speed monitoring

DIA3010-ZPKG/US/3D

Connection

