


RFID read/write head with CAN interface and CANopen protocol

DTMHF GBRWCOUS03



Application

Radio approval for	USA; Canada; EU/RED; Australia; Japan; China; Taiwan; India; Singapore; Ukraine; Brazil
Note on radio approval	The list of countries applying the European Radio Equipment Directive 2014/53/EU (RED) can be found under “Downloads”.

Electrical data

Operating voltage	[V]	9...32 DC
Current consumption	[mA]	< 50 (24 V) / < 80 (12 V)
Protection class		III
Operating frequency	[MHz]	13,56
RFID standard		ISO 15693

Detection zone

Distance write/read head front	[mm]	100
Distance write/read head side	[mm]	50
Distance to the ID tag	[mm]	≤ 18

Interfaces

Communication interface	CAN
CAN	
Protocol	CANopen

Operating conditions

Ambient temperature	[°C]	-40...85
Storage temperature	[°C]	-40...85
Protection		IP 67; IP 69K

Tests / approvals

Shock resistance	EN 60068-2-27	40 g 6 ms / repetitive
	EN 60068-2-27	50 g 11 ms / not repetitive
Vibration resistance	EN 60068-2-6	20 g 10...2000 Hz
MTTF	[ANN]	475

Mechanical data

Weight	[g]	131.5
--------	-----	-------



RFID read/write head with CAN interface and CANopen protocol

DTMHF GBRWCOUS03

Housing	threaded type
Dimensions [mm]	M18 x 1 / L = 70
Thread designation	M18 x 1
Materials	housing: stainless steel; Protective cover: PPS; LED window: PEI

Displays / operating elements


Display	Preoperational Mode	1 x LED, green lights
	Operational Mode	1 x LED, green flashing
	errors	1 x LED, red flashing
	tag communication	1 x LED, yellow lights

Remarks

Pack quantity	1 pcs.
---------------	--------

Electrical connection

Connector: 1 x M12; coding: A



1	not used
2	U+
3	GND
4	CAN_H
5	CAN_L