




RFID read head with AS-Interface

DTSLF AAROASUS01



- 1 integrated antenna
2 tag position mark middle of the antenna



Application

Application	detection of objects on transport equipment
Radio approval for	USA; Canada; EU/RED; Australia; China
Note on radio approval	The list of countries applying the European Radio Equipment Directive 2014/53/EU (RED) can be found under "Downloads".

Electrical data

Operating voltage [V]	26.5...31.6 DC; ("supply class 2" to cULus)
Current consumption [mA]	< 50
Protection class	III
Operating frequency [MHz]	0,125

Outputs

Electrical design	AS-i
-------------------	------

Detection zone

Travel speed [m/s]	< 0.5
Distance read/read head front	200
Distance read/read head side	200



RFID read head with AS-Interface

DTSLF AAROASUS01

Note on distance read/read head	referred to	:	
	Read/write head		DTA100
	Read head		DTA101
Distance write/read head front [mm]	400		
Distance write/read head side [mm]	400		
Note on distance write/read head	referred to	:	
	Read/write head		DTA100
	Read head		DTA101
Distance to the ID tag [mm]	read	:	≤ 20
	static		

Interfaces

Communication interface	AS-i
-------------------------	------

Operating conditions

Ambient temperature [°C]	-20...50
Storage temperature [°C]	-25...80
Protection	IP 67

Tests / approvals

EMC	EN 50295	1999-03
Shock resistance	EN 60068-2-29	40 g 6 ms
	EN 60068-2-27	50 g 11 ms
Vibration resistance	EN 60068-2-6	20 g 10...2000 Hz
MTTF [ANN]	422	

AS-i classification

AS-i I/O configuration [hex]	7
AS-i ID code [hex]	3
AS-i certificate	71502

Mechanical data

Weight [g]	103.2
Housing	rectangular
Dimensions [mm]	55 x 24 x 41
Materials	PA

Displays / operating elements

Display	Operating voltage	1 x LED, green
	tag communication	1 x LED, yellow
	error AS-i data communication	1 x LED, red

Remarks

Remarks	For the distances to other ID tags see the respective data sheet (E803xx)
Pack quantity	1 pcs.

DTA101



RFID read head with AS-Interface

DTSLF AAROASUS01

Electrical connection

Connector: 1 x M12; coding: A



Connection

