


Multifunction display for monitoring analogue standard signals

DISPLAY/AX360/PNP OUT

Article no longer available - archive entry

Alternative articles: DX2042

When selecting an alternative article and accessories please note that technical data may differ!



Application

Application

display of analogue standard signals; e.g. pressure sensors, temperature sensors or flow sensors

Electrical data

Frequency AC	[Hz]	50...60
Operating voltage tolerance	[%]	33...58
Operating voltage	[V]	230 / 115 AC / 24 DC
Current consumption	[mA]	110 (18 V); 90 (24 V); 80 (30 V)
Auxiliary energy for sensors DC	[V]	24; (± 15 %, 150 mA; Short-circuit proof)

Inputs / outputs

Number of inputs and outputs

Number of analogue inputs: 2

Inputs

Number of analogue inputs

2

Outputs

Analogue current output	[mA]	4...20
Analogue voltage output	[V]	0...10

Operating conditions

Ambient temperature

[°C]

0...45



Multifunction display for monitoring analogue standard signals

DISPLAY/AX360/PNP OUT

Storage temperature	[°C]	-25...70
Protection		IP 65; (on the front)
Protection rating terminals		IP 20

Tests / approvals

EMC	EN 50081-1	
	EN 61000-6-2	

Mechanical data

Weight	[g]	552.8
Materials		Noryl UL94-V-0

Displays / operating elements

Display		7-segment LED display, orange 6-digit 15 mm
---------	--	---

Electrical connection

screw terminals, DC: 10 x ...1.5 mm²screw terminals, AC: 4 x ...2.5 mm²

Connection

