


EVC960



Connecting cable with socket

ADOAH050MSE0005C05



Application		
Special feature	Halogen-free; Gold-plated contacts; Screened cable; Drag chain suitability	
Application	CAN bus	
Electrical data		
Operating voltage	[V]	32 DC; (wires 4+5: 5 V)
Max. current load total	[A]	4; (wires 4+5: 0,05 A)
Operating conditions		
Ambient temperature	[°C]	-25...80
Protection	IP 67; IP 68; IP 69K	
Mechanical data		
Weight	[g]	490.05
Dimensions	[mm]	38 x 15.5 x 31.5
Moulded-body material	TPU	
Material nut	brass, nickel-plated	
Sealing material	FKM	
Drag chain suitability	yes	
Drag chain suitability	bending radius for flexible use	min. 10 x cable diameter
	travel speed	max. 3.3 m/s for a horizontal travel length of 5 m and max. acceleration of 5 m/s²
	bending cycles	> 5 Mio.
	torsional strain	± 180 °/m
Remarks		
Remarks	The CAN bus terminating resistor (120 Ω) is integrated in the M12 connector.	
Pack quantity	1 pcs.	



Connecting cable with socket


ADOAH050MSE0005C05

Electrical connection


Cable: 5 m, PUR, Halogen-free, lilac, Ø 8.4 mm, shielded; red / black: 2 x 0.75 mm² (42 x Ø 0.15 mm) + white / blue: 2 x 0.5 mm² (19 x Ø 0.19 mm) + screen: 1 x 0.75 mm² (42 x Ø 0.15 mm)

Electrical connection - socket

Connector: 1 x M12, angled; coding: A; Moulded body: TPU, black; Locking: brass, nickel-plated; Sealing: FKM; Contacts: gold-plated; Tightening torque: 0.6...1.5 Nm



Connection



BK =	Core colours :	black
BU =		blue
RD =		red
WH =		white
screen =		screen