




RFID tag

ID-TAG/51x37x7,5



Application		
Application	RFID coding of metal tanks	
Electrical data		
Operating frequency	[MHz]	866...928
Memory size	[bit]	512
Memory type		EEPROM
Chip type		Alien Higgs 3
Tag identifier (TID)	[Byte]	64
Electronic product code (EPC)		96 bit
RFID standard		EPC Class1 GEN2/ISO 18000-6C
Max. read cycles		unlimited
Max. write cycles		100000
Operating conditions		
Ambient temperature	[°C]	-40...85
Storage temperature	[°C]	-40...250
Protection		IP 69K
Mechanical data		
Weight	[g]	144.5

E80417



RFID tag

ID-TAG/51x37x7,5

Type of mounting	panel / surface
Dimensions [mm]	51 x 36.3 x 7.5
Materials	housing: Nylon / PP

Remarks

Pack quantity	5 pcs.
---------------	--------

Other data

read distance (m)

DTE80x	1.1
DTE90x	-
ANT860 / ANT960	4.8
ANT820 / ANT920	2