


Muting arm set

4P-THROUGH-MULTIBEAM-SENSORS



Product characteristics

Type of light	infrared light
---------------	----------------

Application

Design	sequential muting with four parallel multi-beam light barriers
Function principle	Through-beam sensor

Electrical data

Operating voltage	[V]	19.2...28.8 DC
Current consumption	[mA]	60
Protection class		III
Reverse polarity protection		yes
Type of light		infrared light
Wave length	[nm]	940

Outputs

Electrical design		PNP
Output function		dark-on mode
Max. voltage drop switching output DC	[V]	0.5



Muting arm set

4P-THROUGH-MULTIBEAM-SENSORS

Permanent current rating of switching output DC [mA]	100
Short-circuit protection	yes
Overload protection	yes

Detection zone

Range [m]	< 3.5
-----------	-------

Operating conditions

Ambient temperature [°C]	-30...55
Protection	IP 65

Tests / approvals

EMC	EN 60947-5-2
-----	--------------

Mechanical data

Weight [g]	4295
Materials	aluminium; polypropylene
Lens material	polycarbonate-ABS

Displays / operating elements


Display	transmitter	LED, yellow
	receiver	LED, green/red

Remarks


Pack quantity	4 pcs.
---------------	--------

Electrical connection - receiver 1

Connector: 1 x M12; coding: A; Moulded body: blue



Connection




4 OUT 1	switching output
2 OUT 2	switching output

Muting arm set

4P-THROUGH-MULTIBEAM-SENSORS

Electrical connection - receiver 2


Connector: 1 x M12; coding: A; Moulded body: red

**Connection**

4 OUT 3 switching output
2 OUT 4 switching output


Electrical connection - transmitter 1

Connector: 1 x M12; coding: A; Moulded body: blue



Muting arm set

4P-THROUGH-MULTIBEAM-SENSORS



Connection

2 IN

Sync A

Electrical connection - transmitter 2

Connector: 1 x M12; coding: A; Moulded body: red

**Connection**

2 IN

Sync B