


Inductive area sensor

SIY-3120-BPKG/6M

Article no longer available - archive entry



Product characteristics

Electrical design	PNP
Output function	normally open
Sensing range [mm]	30...120
Housing	cylindrical
Dimensions [mm]	Ø 164 / L = 68

Electrical data

Operating voltage [V]	10...36 DC
Current consumption [mA]	15; (24 V)
Protection class	II
Reverse polarity protection	yes

Outputs

Electrical design	PNP
Output function	normally open
Max. voltage drop switching output DC [V]	2.5
Permanent current rating of switching output DC [mA]	250



Inductive area sensor

SIY-3120-BPKG/6M

Switching frequency DC	[Hz]	3	
Short-circuit protection		yes	
Type of short-circuit protection		pulsed	
Overload protection		yes	
Detection zone			
Sensing range	[mm]	30...120	
Sensing range adjustable		yes	
Factory setting sensing range	[mm]	120	
Real sensing range Sr	[mm]	120 ± 10 %	
Accuracy / deviations			
Correction factor		steel: 1 / stainless steel: 0.7 / brass: 0.4 / aluminium: 0.3 / copper: 0.2	
Hysteresis	[X01]	< 15	
Switch point drift	[X01]	-15...15	
Operating conditions			
Ambient temperature	[°C]	-20...70	
Protection		IP 65	
Tests / approvals			
EMC	EN 60947-5-2		
Mechanical data			
Housing		cylindrical	
Mounting		non-flush mountable	
Type of mounting		with mounting plate	
Dimensions	[mm]	Ø 164 / L = 68	
Materials		housing: PBT; Mounting plate: aluminium anodised	
Displays / operating elements			
Display	switching status		1 x LED, yellow
Remarks			
Pack quantity	1 pcs.		

I27007



Inductive area sensor

SIY-3120-BPKG/6M

Electrical connection

Cable: 6 m, PVC; 3 x 0.5 mm²

Connection



	Core colours :
BK =	black
BN =	brown
BU =	blue