

I7R3020-FPKG/US-100-IPF

- 1 sensitivity
- 2 Output function
- 3 pulse stretching time



yes

I7R209



Inductive ring sensor

I7R3020-FPKG/US-100-IPF

Detection zone		
Resolution of steel ball (diameter)	[mm]	2.5
Max. part speed	[m/s]	35
Response times		
Pulse stretching	[ms]	10...150
Pulse stretching adjustable		yes
Max. fall time	[ms]	10
Response time	[ms]	< 0.5
Operating conditions		
Ambient temperature	[°C]	-25...70
Protection		IP 67
Tests / approvals		
MTTF	[ANN]	658
UL approval	Ta	-25...70 °C
	Enclosure type	Type 4X (indoor use only) / 12 and 13
	подача напруги	Class 2
	File number UL	E174191
Mechanical data		
Weight	[g]	58.4
Housing		circular
Dimensions	[mm]	60 x 35 x 20
Inside diameter	[mm]	20.1
Materials		housing: PA; ring: POM
Displays / operating elements		
Display	switching status	1 x LED, yellow
Remarks		
Pack quantity		1 pcs.
Electrical connection - plug		

Connector: 1 x M12; coding: A



I7R209



Inductive ring sensor

I7R3020-FPKG/US-100-IPF

Connection

