


EVW127



Connection cable

VDOGH050SCS0010T05STGH050SCS



| Application | | |
|---|------|--|
| Special feature | | Free from silicone; Halogen-free; Gold-plated contacts; Drag chain suitability |
| Application | | welding applications |
| Free from silicone | | yes |
| Electrical data | | |
| Operating voltage | [V] | < 60 AC/DC |
| Protection class | | II |
| Max. current load total | [A] | 4 |
| Operating conditions | | |
| Ambient temperature | [°C] | -25...90 |
| Note on ambient temperature | | cULus: ...75 |
| Ambient temperature (moving) | [°C] | -25...90 |
| Note on ambient temperature (moving) | | cULus: ...75 |
| Storage temperature | [°C] | -25...55 |
| Storage humidity | [%] | 10...100 |
| Other climatic conditions for storage according to stated class | | 1K22/ DIN 60721-3-1 |
| Protection | | IP 65; IP 67; IP 68; IP 69K |
| Mechanical data | | |
| Weight | [g] | 428.5 |
| Materials | | housing: TPU orange; Sealing: FKM |
| Material nut | | brass, anti-spatter |



Connection cable


VDOGH050SCS0010T05STGH050SCS

| | | |
|------------------------|---------------------------------|--|
| Drag chain suitability | yes | |
| Drag chain suitability | bending radius for flexible use | min. 10 x cable diameter |
| | travel speed | max. 3.3 m/s for a horizontal travel length of 5 m and max. acceleration of 5 m/s² |
| | bending cycles | > 2 Mio. |
| | torsional strain | ± 180 °/m |

| Remarks | | |
|---------------|---------------------------------|--|
| Remarks | with 2 label holders 30 mm long | |
| Pack quantity | 1 pcs. | |

Electrical connection - plug


Connector: 1 x M12, straight; coding: A; Locking: brass, anti-spatter; Contacts: gold-plated; Tightening torque: 0.6...1.5 Nm



Electrical connection


Cable: 10 m, PUR, Halogen-free, orange, Ø 5.1 mm; not irradiated (can be recycled); resistant to welding sparks; 5 x 0.34 mm² (42 x Ø 0.1 mm)

Connection



Electrical connection - socket

Connector: 1 x M12, straight; coding: A; Locking: brass, anti-spatter; Contacts: gold-plated; Tightening torque: 0.6...1.5 Nm





Connection cable

VDOGH050SCS0010T05STGH050SCS

Diagrams and graphs



Derating $I_{max} * 0.8$ DIN EN 60512-5-2

X Ambient temperature [°C]

Y Current [A]