




Fail-safe inductive sensor

GIGK4008-2PO/SIL2/US



Product characteristics		
Electrical design		PNP
Output function		2 x OSSD (A1 and A2)
Enable zone	[mm]	> 11.5
Housing		threaded type
Dimensions	[mm]	M18 x 1 / L = 60
Application		
Special feature		Gold-plated contacts
Type of operation		permanent operation
Safety-related function		safe state when damped correctly
Application		Застосування в рухомій техніці та складних умовах
Electrical data		
Operating voltage	[V]	8...32 DC
Rated insulation voltage	[V]	60
Current consumption	[mA]	< 20
Protection class		III
Reverse polarity protection		yes
Max. power-on delay time	[ms]	1000
Outputs		
Electrical design		PNP
Output function		2 x OSSD (A1 and A2)
Max. voltage drop switching output DC	[V]	2.5; (30 mA)
Minimum load current	[mA]	1
Permanent current rating of switching output DC	[mA]	50
Switching frequency DC	[Hz]	10
Output data		Interface type C class 1
Output voltage at 24 V		compatible with EN 61131-2 inputs type 1, 2
Short-circuit protection		yes
Overload protection		yes
Max. capacitive load CL_max	[nF]	20



Fail-safe inductive sensor

GIGK4008-2PO/SIL2/US

Detection zone		
Enable zone	[mm]	> 11.5
Safe switch-off distance s(ao)	[mm]	< 6.5
Accuracy / deviations		
Correction factor		steel: 1 / stainless steel: 0.7 / brass: 0.4 / aluminium: 0.4 / copper: 0.3
Hysteresis	[X01]	1...10
Response times		
Response time to safety request	[ms]	5
Response time when approaching the enable zone	[ms]	5
Risk time (response time for safety-related faults)	[ms]	100
Operating conditions		
Ambient temperature	[°C]	-40...85
Max. relative air humidity	[%]	50; (70 °C; <70 °C: >50 %)
Max. height above sea level	[m]	5000
Ionising radiation		not permissible
Protection		IP 65; IP 67; IP 68; IP 69K; (with ifm socket duly screwed on)



Fail-safe inductive sensor

GIGK4008-2PO/SIL2/US

Chemical media

test according to ISO 16750-5	
the following media were tested for 22 hours at 60 °C	coolants
	(HoughtonHocut4480
	Oemeta
	HYCUT ET 46)
The following media were tested for 22 hours at 75 °C	hydraulic fluids
	(Fuchs Renoling B15 VG 46 HLP
	Total BiohydranTMP 4HEES
	Fuchs Hydrotherm 46 M HFC)
	transmission oils
	(Fuchs TITAN ATF 3353 Dexron III)
	diesel
	biodiesel
	urea
	(AdBlue)
	brake fluid
	(K2 TURBO DOT 4)
the following media were tested for 22 hours at 23 °C	corrosion protection
	(Sonax special preservation wax)
	cold cleaner
	(Sonax cold cleaner S)
	ammonia-based cleaner
	(Weco Dr. Webers Salmiak-Konzentrat (concentrated ammonium chloride))
	battery acid
the following media were tested for 2 hours at 23 °C	wheel rim cleaner
	(Sonax Xtreme Plus)
the following media were tested for 10 minutes at 23 °C	premium-grade petrol lead-free



Fail-safe inductive sensor

GIGK4008-2PO/SIL2/US

Tests / approvals								
EMC	industrial environments							
	EN 60947-5-3							
	EN 61000-4-2 ESD	6 kV CD / 8 kV AD						
	EN 61000-4-3 HF radiated	20 V/m						
	EN 61000-4-4 Burst	2 kV						
	EN 61000-4-5 Surge	2 kV						
	EN 61000-4-6 HF conducted	10 V						
	EN 61000-4-8	30 A/m 50/60 Hz / 1000 A/m 0 Hz						
	EN 55011	class B						
	mobile applications	only for operation with central load-dump suppression (58 V) / not for active operation during motor start phase in 12 V systems						
	ISO 10605 ESD	8 kV CD / 15 kV AD						
	ISO 11452-2, ISO 11452-5 radiated immunity	100 V/m						
	ISO 7637-2, ISO 16750-2 conducted immunity	12 V / 24 V						
	pulse	1	2a	3a	3b	4	5b	
	severity level	III	III	III	III	III	III	58V
	failure criterion	B	B	B	A	A	C/B	A
	EN 55025							
Vibration resistance	EN 60068-2-6 Fc	20 g (10...3000 Hz) / 50 sweep cycles, 1 octave per minute, in 3 axes						
Broadband noise	EN 60068-2-64 h	5,9 g (10...2000 Hz) / effective acceleration for chassis mounting						
Shock resistance	EN 60068-2-27 Ea	100 g 11 ms half-sine; 3 shocks each in every direction of the 3 coordinate axes						
Continuous shock resistance	EN 60068-2-27 Ea	40 g 6 ms; 4000 shocks each in every direction of the 3 coordinate axes						
Fast temperature change	EN 60068-2-14 Na	TA = -40°C; TB = 85°C; t1 = 30 min; t2 = 10 s 100 cycles						
Salt spray test	EN 60068-2-52 Kb	severity level 5 (4 test cycles)						
Safety classification								
Complies with the requirements	ISO 13849-1: 2015 category 2, PL d							
	IEC 61508 SIL 2							
	IEC 62061 SIL 2							
Mission time TM	[h]	≤ 87600						
Mission time TM (additional indication)		industrial environments Temperature range -25...70 °C ≤ 175200						
PFH	[1/h]	< 5E-08						
Mechanical data								
Weight	[g]	106.8						
Housing		threaded type						
Mounting		non-flush mountable						
Dimensions	[mm]	M18 x 1 / L = 60						
Thread designation		M18 x 1						
Materials		threaded sleeve: brass white bronze coated; sensing face: LCP; LED window: PEI; lock nuts: brass white bronze coated						
Tightening torque	[Nm]	< 25						

GG854S



Fail-safe inductive sensor

GIGK4008-2PO/SIL2/US

Displays / operating elements

Display	Display switching status	4 LED, yellow
---------	--------------------------	---------------

Аксессуары

Items supplied	lock nuts: 2
----------------	--------------

Remarks


Remarks	material for secure mounting not supplied; fixing must be done by the user
	meets the environmental and EMC requirements for operation in agricultural and forestry machinery, earthworks and construction machines as well as in industrial trucks
	Unless stated otherwise, all data refer to the reference target plate to IEC 60947-5-2 over the whole temperature range.
	(FE360 = ST37-2K) 24x24x1 mm
Pack quantity	1 pcs.

Electrical connection - plug

Connector: 1 x M12; coding: A; Contacts: gold-plated



Connection



1: safety-related logic unit