


Inductive sensor

SIL-2100-ABOW

Article no longer available - archive entry



1 Sensing face



Product characteristics

Output function		normally open
Sensing range	[mm]	25...100
Housing		rectangular
Dimensions	[mm]	400 x 100 x 30

Electrical data

Frequency AC	[Hz]	47...63
Operating voltage	[V]	90...250 AC
Protection class		II
Reverse polarity protection		no

Outputs

Output function		normally open
Max. voltage drop switching output AC	[V]	11
Minimum load current	[mA]	15
Max. leakage current	[mA]	6
Permanent current rating of switching output AC	[mA]	200; (250 (...50 °C))
Short-time current rating of switching output	[mA]	1500; (10 ms / 0,5 Hz)
Switching frequency AC	[Hz]	2
Short-circuit proof		no



Inductive sensor

SIL-2100-ABOW

Overload protection	no	
Detection zone		
Sensing range	[mm]	25...100
Sensing range adjustable		yes
Factory setting sensing range	[mm]	100
Real sensing range Sr	[mm]	100 ± 10 %
Accuracy / deviations		
Correction factor	steel: 1 / stainless steel: 0.7 / brass: 0.4 / aluminium: 0.3 / copper: 0.2	
Hysteresis	[X01]	< 15
Switch point drift	[X01]	-15...15
Operating conditions		
Ambient temperature	[°C]	-20...70
Protection		IP 65
Tests / approvals		
EMC	EN 60947-5-2	
Mechanical data		
Housing		rectangular
Mounting		non-flush mountable
Dimensions	[mm]	400 x 100 x 30
Materials		PVC
Displays / operating elements		
Display	switching status	1 x LED, yellow
Electrical connection		
Required protection	miniature fuse to IEC60127-2 sheet 1; ≤ 2 A; fast acting	
Remarks		
Remarks	Recommendation: Check the safe functioning of the unit after a short circuit.	
Pack quantity	1 pcs.	

I42001



Inductive sensor

SIL-2100-ABOW

Electrical connection

Cable: 2 m, PVC; 2 x 0.5 mm²

Connection



Note miniature fuse to IEC60127-2 sheet 1 $\leq$ 2 A fast acting
Core colours :

BN =

brown

BU =

blue