IA0011

Inductive sensor

IA-2010-ABOW/Sonderkabel

Article no longer available - archive entry

Alternative articles: IA0004

When selecting an alternative article and accessories please note that technical data may differ!



Product characteristics		
Output function		normally open
Sensing range	[mm]	10
Housing		cylindrical
Dimensions	[mm]	Ø 20
Electrical data		
Frequency AC	[Hz]	47...63
Operating voltage	[V]	20...250 AC
Protection class		II
Reverse polarity protection		no
Outputs		
Output function		normally open
Max. voltage drop switching output AC	[V]	5.5
Minimum load current	[mA]	5
Max. leakage current	[mA]	2.5
Permanent current rating of switching output AC	[mA]	300; (500 (...50 °C))
Short-time current rating of switching output	[mA]	2200; (20 ms / 0,5 Hz)
Switching frequency AC	[Hz]	20
Short-circuit protection		no
Overload protection		no

IA0011

Inductive sensor

IA-2010-ABOW/Sonderkabel

Detection zone			
Sensing range	[mm]	10	
Real sensing range Sr	[mm]	10 ± 10 %	
Operating distance	[mm]	0...8.1	
Accuracy / deviations			
Correction factor		steel: 1 / stainless steel: 0.7 / brass: 0.4 / aluminium: 0.3 / copper: 0.2	
Hysteresis	[X01]	1...15	
Switch point drift	[X01]	-10...10	
Operating conditions			
Ambient temperature	[°C]	-25...80	
Protection		IP 67	
Mechanical data			
Housing		cylindrical	
Mounting		non-flush mountable	
Dimensions	[mm]	Ø 20	
Materials		PBT	
Displays / operating elements			
Display		switching status	1 x LED, yellow
Аксесуари			
Items supplied		кріпильні хомути: 1	
Remarks			
Pack quantity		1 pcs.	
Electrical connection			

Cable: 2 m; 2 x 0.75 mm²

Connection



Core colours :
BN = brown
BU = blue