

Inductive sensor

IA-3010-APKG



Product characteristics

Electrical design	PNP
Output function	normally closed
Sensing range [mm]	10
Housing	cylindrical
Dimensions [mm]	Ø 20 / L = 77

Electrical data

Operating voltage [V]	10...36 DC
Current consumption [mA]	15; (24 V)
Protection class	II
Reverse polarity protection	yes

Outputs

Electrical design	PNP
Output function	normally closed
Max. voltage drop switching output DC [V]	2.5
Permanent current rating of switching output DC [mA]	250
Switching frequency DC [Hz]	300
Short-circuit protection	yes
Type of short-circuit protection	pulsed
Overload protection	yes

Detection zone

Sensing range [mm]	10
Real sensing range Sr [mm]	10 ± 10 %
Operating distance [mm]	0...8.1

Accuracy / deviations

Correction factor	steel: 1 / stainless steel: 0.7 / brass: 0.4 / aluminium: 0.3 / copper: 0.2
Hysteresis [X01]	1...15
Switch point drift [X01]	-10...10


IA5050



Inductive sensor

IA-3010-APKG

Operating conditions		
Ambient temperature	[°C]	-25...80
Protection		IP 67
Tests / approvals		
EMC		EN 60947-5-2
MTTF	[ANN]	1844
Mechanical data		
Weight	[g]	127.7
Housing		cylindrical
Mounting		non-flush mountable
Dimensions	[mm]	Ø 20 / L = 77
Materials		PBT
Displays / operating elements		
Display	switching status	1 x LED, yellow
Акcesуари		
Items supplied		кріпильні хомути: 1
Remarks		
Pack quantity		1 pcs.
Electrical connection		
Cable: 2 m, PVC; 3 x 0.5 mm²		
Connection		



Core colours :
BN = brown
BU = blue
BK = black