




Inductive sensor

IDE2060RFB0A/POTI VERS RT



Product characteristics	
Electrical design	series connection possible
Output function	normally open / normally closed; (selectable)
Sensing range [mm]	60; (fixed: 60)
Housing	rectangular
Electrical data	
Operating voltage [V]	20...250 AC/DC
Protection class	II
Reverse polarity protection	no
Outputs	
Electrical design	series connection possible
Output function	normally open / normally closed; (selectable)
Max. voltage drop switching output DC [V]	6.5
Max. voltage drop switching output AC [V]	6.5
Minimum load current [mA]	5
Max. leakage current [mA]	3 (250V AC) / 1.0 (24V DC)
Permanent current rating of switching output AC [mA]	250; (350 (...50 °C))
Permanent current rating of switching output DC [mA]	100
Short-time current rating of switching output [mA]	2200; (20 ms / 0,5 Hz)
Switching frequency AC [Hz]	4



Inductive sensor

IDE2060RFB0A/POTI VERS RT

Switching frequency DC	[Hz]	4	
Short-circuit proof		no	
Overload protection		no	
Detection zone			
Sensing range	[mm]	60; (fixed: 60)	
Real sensing range Sr	[mm]	60 ± 10 %	
Operating distance	[mm]	0...48.6	
Accuracy / deviations			
Correction factor		steel: 1 / stainless steel: 0.7 / brass: 0.4 / aluminium: 0.4 / copper: 0.3	
Hysteresis	[X01]	1...15	
Switch point drift	[X01]	-10...10	
Operating conditions			
Ambient temperature	[°C]	-25...80	
Protection		IP 65	
Tests / approvals			
EMC		EN 60947-5-2	
		EN 55011	class B
MTTF	[ANN]	459	
Mechanical data			
Weight	[g]	434.5	
Housing		rectangular	
Mounting		non-flush mountable	
Materials		PPE	
Displays / operating elements			
Display		switching status	1 x LED, red
Electrical connection			
Required protection		miniature fuse to IEC60127-2 sheet 1; ≤ 2 A; fast acting	
Аксессуары			
Items supplied		screwdriver: 1	
Remarks			
Remarks		Recommendation: Check the safe functioning of the unit after a short circuit.	
Pack quantity		1 pcs.	





Inductive sensor

IDE2060RFBOA/POTI VERS RT

Electrical connection

terminals: ...2.5 mm²

Connection

Note miniature fuse to IEC60127-2 sheet 1 ≤ 2 A fast acting