


Inductive sensor

IDC4050BCPKG/F/2LED/US-100-DPA



Product characteristics

Electrical design	PNP
Output function	complementary
Sensing range [mm]	50
Housing	rectangular
Dimensions [mm]	92 x 80 x 40

Electrical data

Operating voltage [V]	10...36 DC
Current consumption [mA]	20; (24 V)
Protection class	II
Reverse polarity protection	yes

Outputs

Electrical design	PNP
Output function	complementary
Max. voltage drop switching output DC [V]	2.5
Permanent current rating of switching output DC [mA]	250
Switching frequency DC [Hz]	70
Short-circuit protection	yes
Type of short-circuit protection	pulsed
Overload protection	yes

Detection zone

Sensing range [mm]	50
--------------------	----



Inductive sensor

IDC4050BCPKG/F/2LED/US-100-DPA

Real sensing range S_r	[mm]	50; (mounted flush with mild steel (ST37))
Operating distance	[mm]	0...40.5; (mounted flush with mild steel (ST37); non flush: operating distance reduced by max. 5.5 mm)

Accuracy / deviations

Correction factor		steel: 1 / stainless steel: 0.85 / brass: 0.48 / aluminium: 0.46 / copper: 0.38
Hysteresis	[X01]	3...20
Switch point drift	[X01]	-15...15

Operating conditions

Ambient temperature	[°C]	-25...70
Protection		IP 67

Tests / approvals

EMC	EN 60947-5-2	
-----	--------------	--

Mechanical data

Weight	[g]	423.5
Housing		rectangular
Mounting		flush mountable
Type of mounting		rail; (TH35 (EN 60715))
Dimensions	[mm]	92 x 80 x 40
Materials		PPE black; brass white bronze coated; diecast zinc

Displays / operating elements

Display	switching status	1 x LED, yellow
	operation	1 x LED, green

Аксессуары

Items supplied	sealing plug: 1
----------------	-----------------

Remarks

Pack quantity	1 pcs.
---------------	--------

Electrical connection - plug

Connector: 1 x M12; coding: A





Inductive sensor

IDC4050BCPKG/F/2LED/US-100-DPA

Connection

